

6.02012.00 AS 20 L


1200 Watt All-purpose Vacuum Cleaner AS 20 L



- Mobile, compact vacuum cleaner for liquids and dry solids with commercial registration
- Certified for extracting dust particles of dust class L (AGW values $\geq 1 \text{ mg/m}^3$)
- Also suitable for absorbing non-flammable liquids
- Automatic shutoff that is disconnected while absorbing the suction flow as soon as the maximum filling height of the container is reached
- Special air cooling system for long service life of the powerful motor
- Sturdy and washable pleated filter with large surface against quick clogging
- Easy and quick filter change
- Option to wind up the cable
- Practical accessory case and storage area

Comparative technical values

Air output (at fan)	4.200 l/min
Vacuum	210 hPa (mbar)
Filter surface	3.600 cm ²



Rated input power	1.200 W
Container volume	20 l
Suction hose:	
- Diameter	35 mm
- Length	1,75 m
Weight	5 kg

Scope of delivery

Suction hose (Ø 35 mm, 1.75 m long), 2 suction pipes, 1 Cellulose pleated filter, Grouting nozzle, Floor nozzle (260 mm wide)