YORKEX H/HARD (T/X)			YORKEX HARD			YORKEX CHROME PLATED						
	O/D			Press	O/D	6. 1.1.1		Press	O/D	6. 1.1.1		Press
	Wall	Stock Lth		65C	Wall	Stock Lth		65C	Wall	Stock Lth		65C
	MM	3mtr	6mtr	Bar	MM	3mtr	6mtr	Bar	MM	3mtr	6mtr	Bar
1	2x0.6	✓	*	63	35x1.0	✓	✓	42	15x0.7	✓	✓	58
1	5x0.7	✓	✓	58	42x1.0	✓	✓	35	22x0.9	✓	✓	51
2	2x0.9	✓	✓	51	54x1.0	✓	✓	27	28x0.9	✓		40
2	8x0.9	✓	✓	40	67x1.2	✓	✓	26	35x1.2	✓		51
3	5x1.2	✓	✓	42	76x1.5	✓	✓	29	42x1.2	✓		42
4	2x1.2	✓	✓	35	108x1.5	✓	✓	20	54x1.2	✓		33
5	4x1.2	✓	✓	27								

	KUTERLON (T/Y)			KUTERLON PLASTIC COATED			MINIBORE ANNEALED				
O/D			Press	O/D			Press	O/D			Press
Wall	3mtr		65C	Wall	6mtr	25mtr	65C	Wall	10mtr	25mtr	65C
MM	LTHS		Bar	MM	LTHS	Coil	Bar	MM	Coil	Coil	Bar
12x0.8	✓		67	8x0.6		✓	66	6x0.6		✓	90
15x1.0	✓		87	10x0.7		✓	62	8x0.6	✓	✓	66
22x1.2	✓		69	15x0.7	✓	✓	58	10x0.6	✓	✓	62
28x1.2	✓		56	15x1.0		✓	67				
35x1.5	✓		65	22x1.2	✓	✓	57				
42x1.5	✓		54								
54x2.0	✓		56								

Yorkshire copper tube 6-159mm, can be trusted to convey fluids/gases ranging from -196c+205c Yorkshire copper carries a 25 year guarantee against product failure directly attributable to a manufacturing defect. Please contact our sales office for the suitability of each product range. This is a sample range that Yorkshire copper offer, see their full catalogue for further details.



CHOICE AND QUALITY FROM YORKSHIRE

- Yorkex and Kuterlon general purpose plain tube Minibore coils
- Kuterlex and Kuterlex pre-coated tubes for external protection
- WICU Gas yellow pre-coated coils for gas services
- Yorkshire Medical degreased tube (to BS EN 13348) Yorkex Chrome-plated tube

All BSi Kitemark certified and backed by Yorkshire's 25 year guarantee.

Choose Yorkshire Copper Tube: ask for it by name.



Copper Pressfittings 12mm – 108mm (Stock range shown) WRAS/KIWA Approved. Suitable for Hot/Cold & Heating Services



Sanha Copper Pressfittings upto 54mm can be crimped with any press-on clamps & crimping tools available in the market for metal crimp connections (Regular maintenance is absolutely necessary for all tool/clamps & calibration every 12 months)

Copper fittings to BS EN12449 gunmetal fittings to BS EN1982.

Copper pipe to correspond to EN1057 or BS2871

Max temp 120C max pressure PN16, for indication only see manufacturers temp/pressure graph.

Sanha offer a full range of fittings for gas, solar heating (200C), compressed air, stainless steel material & valves including radiator, ball valves & manifolds.

Additional size fittings available please see Sanha full catalogue.

SYSTEM TECHNOLOGY OF SANHA

More Comfortable - Fairer - Safer



www.sanha.com

Copper Pressfittings 12mm – 108mm (Stock range shown) WRAS/KIWA Approved. Suitable for Hot/Cold & Heating Services





Carbon Steel Nirotherm Pressfittings 15-108mm (Stock range shown)
Suitable For Hot/Cold Water, Heating, Clean Air Systems & Industrial Applications

SC1 24270 Straight Coupling 15mm 42mm 18mm 54mm 22mm 76mm 28mm 89mm 35mm 108mm	Reducer Insert 42x22mm 42x28mm 42x35mm 54x35mm 54x42mm	SC21s 24040 45 Str Elbow m/f 15mm 42mm 18mm 54mm 22mm 76mm 28mm 89mm 35mm 108mm
Female Adaptor 15mmx ¹ / ₂ 22mmx ³ / ₄ 28mmx1 35mmx1 ¹ / ₄ 42mmx1 ¹ / ₂	Reducer Insert 76x35mm 76x42mm 76x54mm 89x54mm 89x42mm	SC24 24130 Tee Equal 15mm 42mm 18mm 54mm 22mm 76mm 28mm 89mm 35mm 108mm
Female Adaptor 54mmx2 76mmx2½ 89mmx3	Reducer Insert 108x42mm 108x54mm 108x76mm 108x89mm	Red Branch Tee 22x15mm 28x15mm 28x22mm 35x22mm 35x28mm
Male Adaptor 15mmx ¹ / ₂ 22mmx ³ / ₄ 28mmx1 35mmx1 ¹ / ₄ 42mmx1 ¹ / ₂	SC12 24002A 90 Elbow 15mm 42mm 18mm 54mm 22mm 76mm 28mm 89mm 35mm 108mm	Red Branch Tee 42x22mm 42x28mm 42x35mm 54x35mm 54x42mm
Male Adaptor 54mmx2 76mmx2 ¹ / ₂ 89mmx3	SC12s 24001A 90 Str Elbow m/f 15mm 42mm 18mm 54mm 22mm 76mm 28mm 89mm 35mm 108mm	Red Branch Tee 76x35mm 76x42mm 76x54mm 89x54mm 89x76mm
Reducer Insert 22x15mm 28x15mm 28x22mm	SC21 24041 45 Elbow 15mm 42mm 18mm 54mm 22mm 76mm	Red Branch Tee 108x54mm 108x76mm 108x89mm

SANHA®-Therm - - the most extensive assortment

89mm 108mm

28mm

SANHA®-Therm system fittings are particularly economic alternative to closed systems such as heating and solar plants, as well as compressed air and cooling system applications.

SANHA®-Therm system fittings (series 24000)

35x22mm

Shaped part gasket EPDM. **SANHA®-Therm** fittings are marked with a red dot. They are optimally applicable with **SANHA®-Therm** system pipes (compare table p. 18/19).

SANHA®-Therm system pipes of C steel (series 24000) from d = 12 mm to d = 108 mm

Un-alloyed steel, Material no. 1.0034 (E 195) according to EN 10305, outside zinc plated for the optimal protection from outside corrosion.



Carbon Steel Nirotherm Pressfitting 15-108mm (Stock range shown)
Suitable for Hot/Cold Water, Heating, Clean Air Systems & Industrial Applications




Sanha Carbon Steel Fittings up to 54mm can be crimped with pressing tools & jaws provided for metal connection type M-MM (Please check with Sanha for tool suitability)

Nirotherm tube to Din EN10088, fittings to CW024A/CW617N Max Temp 120C, Max Pressure PN16 (for indication only please check with manufacturers temp/pressure graph)

The economic alternative for closed systems

SANHA®-Therm offers a complete pipe and fitting assortment in the proven SANHA quality for diameters from 12 to 108 mm. The electro galvanising offers secure protection against external corrosion for many decades



Yorkshire Potable integral solder ring fittings 6mm-108mm manufactured to BS EN1254 Part1

YP1	YP6	YP24
Straight Coupling 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm	Reducer Insert 15x8mm	Tee 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm
YP1 IM Imp/Metric Coup 1/2x15mm 3/4x22mm 1x28mm 11/4x35mm 11/2x42mm	YP6 Reducer Insert 42x28mm 54x35mm 42x35mm 54x42mm 54x15mm 67x35mm 54x22mm 67x42mm 54x28mm 67x54mm	YP25 Tee Red branch 22x15mm
YP1R Reducing Coup 15x8mm	YP12 Elbow 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm	YP25 Tee Red branch 42x28mm 54x35mm 42x35mm 54x42mm 54x15mm 67x28mm 54x22mm 76x42mm 54x28mm 76x54mm
Female Conn 15mmx ¹ / ₄ 54mmx2 22mmx ³ / ₄ 28mmx1 35mmx1 ¹ / ₄ 42mmx1 ¹ / ₂	YP12S Street Elbow M/F 15mm 42mm 22mm 54mm 28mm 67mm 35mm 76mm	YP26 TEE One End Reduced 22x15x22
YP3 Male Conn 15mmx½ 54mmx2 22mmx¾ 76mmx3 28mmx1 108mmx4 35mmx1½ 42mmx1½	YP15 Backplate Elbow 15mmx ¹ / ₂ 22mmx ³ / ₄	YP26 TEE One End Reduced 54x42x54mm 67x54x67mm 76x42x76mm 76x54x76mm
YP3LC Male Red Conn 15mmx¹/₄ 15mmx³/₅ 22mmx¹/₂ 28mmx³/₄	YP21 Obtuse Elbow 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm	YP27 TEE End/Branch Red 22x15x15mm 28x15x15mm 28x15x22mm 28x22x15mm 28x22x22mm
Tank Connector 15mmx ¹ / ₂ 54mmx2 22mmx ³ / ₄ 28mmx1 35mmx1 ¹ / ₄ 42mmx1 ¹ / ₂	YP21S 45 M/F Elbow 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm	YP27 TEE End/Branch Red 35x22x22mm 35x28x15mm 35x28x22mm 35x28x22mm 35x28x28mm

We stock from 6mm-108mm, some large 76/108mm fittings are made from gunmetal with wedge ring design.

YORKSHIRE FITTINGS YP RANGE

Yorkshire potable integral solder ring fittings 6mm-108mm manufactured to BS EN1254 Part1

YP69 YP27 TEE YP61 15mmx¹/₂ 42x28x28mm 54mm 15mm 22mmx³/₄ 76mmx3 42x35x28mm 22mm 67mm 28mmx1 108mmx4 42x35x35mm 28mm 76mm 35mmx11/4 54x42x42mm 108mm 35mm 42mmx1¹/₂ 42mm YP28 TEE YP62 **YP69 F** 8x15mm 35x42mm 15mmx¹/₂ 15mmx¹/₂ 54mmx2 42x54mm 22mmx³/₄ 15x22mm 15mmx3/4 15x28mm 28mmx1 22mmx¹/₂ 35mmx11/4 22x28mm 22mmx³/₄ 28x35mm 42mmx11/2 YP29 TEE **YP63 YP415GM** One End BS 35mm 15mm $15x^{1}/_{2}x15mm$ 15mmx¹/₂ 22mm 42mm 22x3/4x22mm 22mmx¹/₂ 28mm 54mm 28x1x28mm 22mmx³/₄ YP29R TEE **YP65** YP151 LS **Red End BSP** 22x1/2x22mm 15mmx¹/₂ 15mm 35mm 54mmx2 $28x^{1}/_{2}x28mm$ 22mmx3/4 22mm 42mm 28x3/4x28mm 28mmx1 28mm 54mm $35x^{1}/_{2}x35mm$ 35mmx11/4 42mmx11/2 YP65F YP501 YP30 TEE Fem BSP Branch 15mmx¹/₂ 15mmx¹/₂ 54mmx2 15mm 35mm 42mm 22mm 22mmx3/4 22mmx3/4 28mmx1

YP30R TEE						
Fem BSP Branch						

22mmx¹/₂ 42mmx¹/₂ 28mmx¹/₂ 28mmx³/₄ $35 \text{mmx}^{1}/_{2}$



28mmx1 35mmx1¹/₄ 42mmx1¹/₂








Yorkshire offer additional fittings & sizes to the above, please ask for full product guide.

Yorkshire potable fittings are also available in chrome plated, general high duty & waste.





The Push Fit Jointing System Manufactured From DZR Copper Alloy To EN1254



A full range from 10mm to 54mm is available in stainless steel.

Tectite is designed to push together in seconds creating a perfect heat free installation joint. Ideal for jointing copper & chrome plated tube to BS EN1257 PEX and PB plastic pipe.

Tectite fittings are WRAS approved for use on hot & cold water services & heating.

NOT FOR USE ON GAS.



Endex range of end feed capillary fittings 6mm to 219mm manufactured to BS EN1254 Part 1

N1 Straight Coupling 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm	Reducer Insert 42x28mm 54x35mm 42x35mm 54x42mm 54x15mm 67x28mm 54x22mm 67x35mm 54x28mm 67x42mm	N21 Obtuse Elbow 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm
N1R Reducing Coup 15x10mm	N6 Reducer Insert 76x35mm 76x42mm 76x54mm 76x67mm	N21S 45 Str Elbow M/F 15mm 35mm 22mm 42mm 28mm 54mm
N1 SLIP Coupling 15mm 35mm 22mm 42mm 28mm 54mm	N6 Reducer Insert 108x42mm 108x54mm 108x67mm 108x76mm	N24 Tee 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm
Female Conn 15mmx ¹ / ₂ 42mmx1 ¹ / ₂ 22mmx ³ / ₄ 54mmx2 28mmx1 35mmx1 ¹ / ₄	N7 Female Adaptor 15mmx½ 54mmx2 22mmx¾ 28mmx1 35mmx1¼ 42mmx1½	N25 Tee Red Branch 22x15mm 35x28mm 28x15mm 42x15mm 28x22mm 42x22mm 35x15mm 42x28mm 35x22mm
N3 Male Conn 15mmx½ 54mmx2 22mmx¾ 67mmx2½ 28mmx1 76mmx3 35mmx1¼ 108mmx4 42mmx1½	N12 Elbow 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm	N25 Tee Red Branch 42x35mm 54x42mm 54x15mm 67x28mm 54x22mm 76x35mm 54x28mm 76x42mm 54x35mm 76x54mm
N5 Tank Connector 15mmx\frac{1}{2} 22mmx\frac{3}{4} 28mmx1	Street Elbow M/F 15mm 35mm 22mm 42mm 28mm 54mm	N26 TEE One End Reduced 22x15x22
N6 Reducer Insert 15x8mm	N15 Backplate Elbow 15mmx¹/₂ 22mmx³/₄	N27 TEE End/Branch Red 22x15x15mm 28x15x15mm 28x15x22mm 28x22x15mm 28x22x22mm

Above items are for indication only other sizes available on request.

Endex range of end feed capillary fittings 6mm to 219mm manufactured to BS EN1254 Part 1

N62 N27 TEE N29R TEE End/Branch Red 35x22x22mm 22x¹/₂x22mm $15 mmx^{1/2}$ 35x28x15mm 28x1/2x28mm 15mmx³/₄ 28x³/₄x28mm 35x28x22mm 22mmx3/4 35x28x28mm N27 TEE N63 N₃0 TEE 15mmx¹/₂ 42x28x28mm 15mmx¹/₂ 42x35x28mm 22mmx³/₄ 15mmx³/₄ 28mmx1 22mmx³/₄ 42x35x35mm 54x42x42mm N28 TEE N30R TEE N65 **Both Ends Red** 15x22mm 22mmx¹/₂ 15mmx¹/₂ 54mmx2 15x28mm 28mmx1/2 22mmx3/4 22x28mm 28mmx³/₄ 28mmx1 28x35mm 35mmx1¹/₄ 35x42mm 42mmx11/2 N29 TEE **N61 N69** 15mmx¹/₂ 54mmx2 15x¹/₂x15mm 15mm 54mm 22x³/₄x22mm 22mm 67mm 22mmx³/₄ 22x1/2x22mm 28mm 28mmx1 76mm 35mmx1¹/₄ 35mm 108mm 42mmx1¹/₂ 42mm



Capillary fittings that are light and easy to handle simple to install by applying heat from a blow torch & solder to the mouth of the fitting.

- Sizes from 6mm to 54mm for use with soft or hard solder sizes from 67mm to 159mm for use with high temperature brazing alloys
- Manufactured from copper, gunmetal or DZR to EN 1254
- WRAS approved with 25 year guarantee





www.pegleryorkshire.co.uk

Aalberts Industries Brass compression fittings BS EN1254-2,6mm-108mm (stock range shown) Additional fittings available to order

610 Straight Coupling 6mm 28mm 8mm 35mm 10mm 42mm 15mm 22mm	611TC BSPP Tank Coupling 42mmx1½ 54mmx2 67mmx2½ 76mmx3	616 BSPT Male Elbow 22mmx³/₄ 22mmx1 28mmx1
610 Straight Coupling 54mm 67mm 76mm 108mm	612 BSPP Female Coupling 8mmx ¹ / ₄ 10mmx ¹ / ₄ 10mmx ³ / ₆ 15mmx ¹ / ₂ 15mmx ³ / ₄	616 BSPT Male Elbow 35mmx1 ¹ / ₄ 42mmx1 ¹ / ₂ 54mmx2 67mmx2 ¹ / ₂
611 BSPT Male Coupling 6mmx ¹ / ₈ 6mmx ¹ / ₄ 8mmx ¹ / ₄ 10mmx ¹ / ₈	612 BSPP Female Coupling 22mmx³/4 22mmx1 28mmx1	617 BSPP Female Elbow 8mmx¹/₄ 28mmx1 10mmx³/₅ 15mmx¹/₂ 22mmx³/₄ 22mmx1
611 BSPT Male Coupling 15mmx½ 15mmx¾ 22mmx¾ 22mmx1 28mmx1	612 BSPP Female Coupling 35mmx1 ¹ / ₄ 42mmx1 ¹ / ₂ 54mmx2 67mmx2 ¹ / ₂ 76mmx3	617 BSPP Female Elbow 35mmx1 ¹ / ₄ 42mmx1 ¹ / ₂ 54mmx2
611 BSPT Male Coupling 15mmx ³ / ₈ 22mmx ¹ / ₂ 28mmx ³ / ₄ 35mmx1 35mmx1 ¹ / ₄	615 Elbow 6mm 28mm 8mm 10mm 15mm 22mm	617W BSPP Blackplate Elbow 15mmx³/₂ 15mmx³/₄ 22mmx²/₂ 22mmx³/₄
611 BSPT Male Coupling 42mmx1½ 54mmx2 67mmx2½ 76mmx3 108mmx4	615 Elbow 35mm 108mm 42mm 54mm 67mm 76mm	618 Tee 6mm 8mm 10mm 15mm 22mm
611TC BSPP Tank Coupling 15mmx ¹ / ₂ 22mmx ³ / ₄ 28mmx1 35mmx1 ¹ / ₄	616 BSPT Male Elbow 8mmx¹/₄ 10mmx²/₅ 15mmx¹/₂ 15mmx²/₄	618 Tee 28mm 76mm 35mm 108mm 42mm 54mm 67mm

Brass compression Fittings BS EN1254-2, 6mm-108mm (stock range shown) Additional fittings available to order



DZR compression fittings to BS EN1254-2 are available to order & should be specified when water conditions are such that standard brass fittings may suffer corrosion.

Compression ranges available in metric MDPE, copper/chrome waste fittings & traps.



Easy to assemble Kuterlite compression fittings are simple and reliable mechanical joints that can be broken and re-made with the use of spanners. Kuterlite fittings are available in both Brass and DZR to EN 1254 Part 2.

- Available in sizes 6 to 108mm
- Compatible with copper tube and on sizes up to 28mm with carbon steel and stainless steel tube, PEX and PB pipe
- WRAS approved with 25 year guarantee





CHROME PLATED BRASS COMPRESSION FITTINGS BS EN1254-2 STOCK SIZES SHOWN.6mm-54mm AVAILABLE & POLISHED CHROME TO SPECIAL ORDER





WE STOCK TUBE SIZES FROM 15mm-54mm

CHROME PLATED COPPER TUBE EN1057 IN 3MTR LTHS

