

## **GHG 660 LCD Professional**



## The heat gun with the greatest ease of use

- 4 main applications can be stored permanently, so that airflow and temperature are at the correct setting instantly
- Airflow and temperature control in steps of ten for precise working; data is shown on an LCD display
- Heating automatically switches off and cools when overheating, for long lifetime
- Cold setting: heating element cools down within approx. 1 minute
- Removable coarse dirt filter for cleaning
- Ergonomic design and softgrip

Rated power input	2.300 W
Weight	1,0 kg
Length	255 mm
Height	255 mm
Specifications, use	
Working temperature	50 − 660 °C
Airflow	250 – 500 l/min
Control, airflow	infinitely variable