

Canon PIXMA iP7250 Inkjet Printer



Fast, low-profile photo printer with Wi-Fi, Auto Duplex and Direct Disc print.

High performance photo printer with 5 individual inks, Wi-Fi connectivity and smartphone printing. Low-profile design with two fully integrated paper trays, Auto Duplex and Direct Disc Print.

- High performance 5-ink photo printer with Wi-Fi
- Photolab quality printing, fast
- Low-profile design with integrated paper trays
- Mobile printing & Apple AirPrint
- My Image Garden software
- Direct Disc Print & Auto Duplex
- Print more with optional XL inks





Only change the ink which runs out



Superb photolab-quality print head



Micro ink droplets for precise print



High resolution photo printing



Print directly onto disc



Automatic double sided printing



Use and share wirelessly



Tablet and Smartphone ready



One-stop creative software



Print images from your movies



Facebook photo printing



Optional high yield inks

GENERAL SPECIFICATIONS

Main Functions	Document and photo printing
Other Functions	Double sided documents Printing on disc surface Smartphone and tablet printing AirPrint support
What's in the box	Printer, 5 Ink tanks, Power cord, Setup guide, CD-Printing Tray, Software and User's manual CD

PRINTER SPECIFICATIONS

Print Resolution	Up to 9600 ¹ x 2400 dpi
Print Engine	Inkjet FINE print head technology 5-colour system with min. 1pl ink droplet size 5 Individual Ink Tanks with ChromaLife100+
Mono Document Print Speed	ESAT: Approx. 15.0 ipm ¹
Colour Document Print Speed	ESAT: Approx. 10.0 ipm ¹
Photo Print Speed	Borderless 10x15cm : Approx. 21 seconds ¹

Borderless Printing	Yes (A4, Letter, 20x25cm, 13x18cm, 10x15cm)
Two Sided Printing	Auto Duplex Print (A4, A5, B5, Letter)
Direct Disc Printing	Yes (software included)
Other Print Features	Fit-to-Page print, Scaled print, Multiple page per sheet print, Booklet print, Poster print, Collate ¹

INK AND PAGE YIELD

Standard Ink Cartridges	5 individual ink tanks PGI-550PGBK (Pigment Black) CLI-551BK (Black) CLI-551C (Cyan) CLI-551M (Magenta) CLI-551Y (Yellow)
Optional Ink Cartridges	High yield XL ink tanks PGI-550PGBK XL (Pigment Black) CLI-551BK XL (Black) CLI-551C XL (Cyan) CLI-551M XL (Magenta) CLI-551Y XL (Yellow)
Ink Tank Life - Document Printing	A4 Colour Document ¹ Pigment Black: 300 pages Pigment Black XL: 500 pages Black: 1795* pages Black XL: 5530* pages Cyan: 332 pages Cyan XL: 695 pages Magenta: 319 pages Magenta XL: 680 pages Yellow: 344 pages Yellow XL: 695 pages * Estimated supplemental yield
Ink Tank Life - Photo Printing	10x15cm photo ¹ Pigment Black: 2425* photos Pigment Black XL: 5615* photos Black: 376* photos Black XL: 1130* photos Cyan: 121 photos Cyan XL: 267 photos Magenta: 132 photos

	Magenta XL: 313 photos Yellow: 130 photos Yellow XL: 274 photos * Estimated supplemental yield
--	---

PAPER SUPPORT

Paper Types	Plain Paper, Envelopes, Photo Paper Pro Platinum (PT-101), Photo Paper Plus Glossy II (PP-201), Photo Paper Pro Luster (LU-101), Photo Paper Plus Semi-gloss (SG-201), Glossy Photo Paper "Everyday Use" (GP-501), Matte Photo Paper (MP-101), High Resolution Paper (HR-101N), T-shirt Transfer (TR-301), Photo Stickers (PS-101)
Maximum Paper Input	Lower cassette: Max. 125 sheets (plain paper) Upper cassette: Max. 20 sheets (photo paper) Direct Disc Print Tray: 1 printable CD, DVD or Blu-Ray Disc
Paper Sizes	Lower cassette: A4, A5, B5, Letter, Legal, Envelopes (DL size or Commercial 10), 20x25cm Upper cassette: 10x15cm, 13x18cm
Paper Weight	Lower cassette: Plain paper: 64 - 105 g/m ² , Photo paper up to approx. 300 g/m ² (Canon special media) Upper cassette: Photo paper up to approx. 300 g/m ² (Canon special media)

INTERFACE

Interface Type - PC / Mac	Hi-Speed USB (B Port) Wi-Fi: IEEE802.11 b/g/n Wi-Fi Security: WPA-PSK, WPA2-PSK, WEP
Interface Type - Non PC	Android devices, iPhone, iPod touch and iPad ¹ Apple AirPrint

SOFTWARE

Included Software	Printer driver My Image Garden CREATIVE PARK PREMIUM access Full HD Movie Print ¹ Quick Menu Easy-WebPrint EX (download) ²
Supported Operating Systems	Windows 8 (32 and 64bit) Windows RT Windows 7 (32 and 64bit) Windows Vista SP1, SP2 (32 and 64bit) Windows XP SP3 (32bit)

	Mac OS X 10.5.8 - 10.8
Windows System Requirements	Windows 7: 1GHz or faster CPU, 1GB RAM (32bit) / 2GB RAM (64bit) Windows Vista SP1 or SP2: 1GHz or faster CPU, 512MB RAM Windows XP SP3: 300MHz or faster CPU, 128MB RAM Browser: Internet Explorer 6 or higher CD-ROM Drive Display: 800 x 600 or better
Mac System Requirements	Mac OS X v10.7: Intel Core2Duo (or higher) CPU, 1GB RAM Mac OS X v10.6: Intel CPU, 1GB RAM Mac OS X v10.5.8: Intel CPU, 512MB RAM Browser: Safari 3 or higher CD-ROM Drive Display: XGA 1024 x 768 or better

PHYSICAL FEATURES

Weight	Approx. 6.6 kg
Dimensions (W x D x H)	451 x 368 x 128mm
Acoustic Noise Levels	Approx. 44.4 dB ¹
Operating Temperature	5-35°C
Operating Humidity	10-90%RH (no dew condensation)
Power Source	AC 100-240V, 50/60Hz
Power Consumption	Standby: approx. 2.1 W (Wi-Fi connection) Off: approx. 0.3 W Printing: approx. 24 W (Wi-Fi connection) ¹
Print Resolution	¹ Ink droplets can be placed with a minimum pitch of 1/9600 inch
Mono Document Print Speed	¹ Document print speed on plain paper is measured based on average of ESAT in Office Category Test of ISO/IEC 24734 standard.
Colour Document Print Speed	¹ Document print speed on plain paper is measured based on average of ESAT in Office Category Test of ISO/IEC 24734 standard.

Photo Print Speed	¹ Photo print speed is based on default driver setting using ISO/JIS-SCID N2 standard on Canon Photo Paper Plus Glossy II and does not take into account data processing time on host computer.
Other Print Features	¹ Some features available in Windows driver only.
Ink Tank Life - Document Printing	¹ Declared yield value in accordance with ISO/IEC 24711 standard. Values obtained by continuous printing.
Ink Tank Life - Photo Printing	¹ Declared yield value in accordance with ISO/IEC 29102. Values obtained by continuous printing.
Interface Type - Non PC	¹ Requires connection over Wi-Fi network and installation of free Canon application: EPP for Android and iEPP for iOS. Not available in certain countries or regions.
Included Software	¹ Full HD Movie Print is available for MOV and MP4 movie files created by select Canon digital cameras and camcorders. Requires installation of software bundled with Canon video or digital camera, from which the movie was captured. MOV files require: ZoomBrowser EX / ImageBrowser (version 6.5 or later), MP4 files require: ImageBrowser EX (version 1.0 or later). ² Easy-WebPrint EX requires Internet Explorer 7 or later
Acoustic Noise Levels	¹ When printing ISO/JIS-SCID N2 pattern on 10x15cm Photo Paper Plus Glossy II using default settings.
Power Consumption	¹ When printing ISO/JIS-SCID N2 on A4 size plain paper using default settings.

- All specifications subject to change without notice.
- Print speed may vary depending on system configuration, interface, software, document complexity, print mode, page coverage, type of paper used etc.
- Ink yield may vary depending on texts/photos printed, applications software used, print mode and type of paper used. For yield information see www.canon-europe.com/ink/yield
- All brand and product names are trademarks of their respective companies.
- Microsoft, Windows and the Windows logo are trademarks, or registered trademarks of Microsoft Corporation in the United States and/or other countries.
- For more information on ChromaLife100+ please visit www.canon-europe.com/chromalife100.