





VAHS-25-0028-5M
REV.*VOLEX SZ
SN:2500285YYDDDDXXXX
|||||

S/N	DESCRIPTION	ITEM NO.	QTY
1	CABLE OPTIONS		
1.1	2PX25AWG 100 OHM BLACK, LEONI	CBHS-25-0005	A/R
2	SFP+ CABLE END CONN	CNHS-05-0015	2
3	PASSIVE SFP+ PCBA	PCAP-01-0033	2
4	LABEL	LABL-02-0050	1
5	S/R MOLD	PVC 75A	A/R
6	DUST COVER	49.0006SZ	A/R
7	STATIC BAG	PACK-02-0019	A/R

SN:2500285YYDDDDXXXX
P/N'S Abbreviation
2:Representative Length
Four serial number
YY=numeric;year(e.g.2011=11)
DDD=numeric;work day among the year.



RX-	12	19	TX-
RX+	13	18	TX+
TX+	18	13	RX+
TX-	19	12	RX-

WIRING TABLE



☐ Hermosillo, MX
☐ Hickory, NC
☐ Indianapolis, IN
☐ Kanata, Canada
☐ Suzhou, China
☐ Tijuana, Mexico

FORM No: 01-(TL)ENG-076-FM001(C)

Proprietary Notice

This document is the property of Volex Inc. The information contained herein is not to be disclosed to anyone without the express written consent of Volex Inc.

REV.	EOR No.	RELEASE FOR PRODUCTION	DATE	JACK ZHANG
X1			2/1/13	
TOLERANCE UNLESS OTHERWISE SPECIFIED .XXX ± .005 .XX ± .02 .X ± .3 FRACT. ± 1/32" ANGULAR ± 1/2"				
DRAWN JACK ZHANG DATE 2/1/13				
ENG'R ZHANG DATE 2/1/13				
APPR'D DATE 2/1/13				
CHENG M				
UNIT: MM				
SCALE SIZE SHEET 1 OF 1				
ROHS COMPLIANT: YES				
MODEL FILE N/A				
PART NO. VAHS-25-0028-5M				
DRAWING NO. VAHS-25-0028-5M				