


S/N	DESCRIPTION	ITEM NO.	QTY
1	INFINIBAND 8PAIR 100 OHM 28AWG,BALCK	CBHS-28-0087	A/R
2	LABEL	LABL-02-0043	1
3	L/P EXT mSAS CABLE END CONN (KEY:2.4.6)	CNHS-06-0024	2
4	MINI SAS EXT PCB,PLATING AU 30U"	PCBP-02-0013	2

VAHS-28-0133-3M
REV.* VSZ YYWW
MADE IN CHINA



GROUND	A1	B1	GROUND
RX0+	A2	B2	TX0+
RX0-	A3	B3	TX0-
GROUND	A4	B4	GROUND
RX1+	A5	B5	TX1+
RX1-	A6	B6	TX1-
GROUND	A7	B7	GROUND
RX2+	A8	B8	TX2+
RX2-	A9	B9	TX2-
GROUND	A10	B10	GROUND
RX3+	A11	B11	TX3+
RX3-	A12	B12	TX3-
GROUND	A13	B13	GROUND
P1		P2	
GROUND	B1	A1	GROUND
TX3-	B2	A2	RX3-
TX3+	B3	A3	RX3+
GROUND	B4	A4	GROUND
TX2-	B5	A5	RX2-
TX2+	B6	A6	RX2+
GROUND	B7	A7	GROUND
TX1-	B8	A8	RX1-
TX1+	B9	A9	RX1+
GROUND	B10	A10	GROUND
TX0-	B11	A11	RX0-
TX0+	B12	A12	RX0+
GROUND	B13	A13	GROUND
SHELL		SHELL	

WIRING TABLE



- ☐ Hermosillo, MX
- ☐ Hickory, NC
- ☐ Indianapolis, IN
- ☐ Kanata, Canada
- ☒ Suzhou, China
- ☐ Tijuana, Mexico

FORM No: 01-(TL)ENG-076-FM001(C)

Proprietary Notice

This document is the property of Vollex Inc. The information contained herein is not to be disclosed to anyone without the express written consent of Vollex Inc.

REV.	ECR No.	RELEASE FOR PRODUCTION	jack zhong	DATE
X1				2/1/13

TOLERANCE UNLESS OTHERWISE SPECIFIED .XXX ± .005 .XX ± .02 X ± .03 FRACT. ± 1/32" ANGULAR ± 1/2°

DRAWN	DATE	DESCRIPTION	ITEM DESCRIPTION
jack zhong	2/1/13		External Mini SAS Cable 3M 28AWG

ENGR Terry DATE 2/1/13 APPRD DATE 2/1/13 CHENG M

UNIT: MM SCALE SIZE SHEET 1 OF 2

ROHS COMPLIANT: YES PART NO. VAHS-28-0133-3M MODEL FILE N/A DRAWING NO. VAHS-28-0133-3M