

Routers



| Model Number | DW615 | DW624 | DW625EK | DW626 |
|----------------------|------------------|-----------|----------------|----------------|
| Input Power | 900 W | 1600 W | 2000 W | 2300 W |
| No Load Speed | 8000 - 24000 rpm | 20000 rpm | 8000-20000 rpm | 8000-21000 rpm |
| Tool Holder | 6-6.35 mm | 6-12.7 mm | 6-12.7 mm | 8-12 mm |
| Maximum Plunge Depth | 55 mm | 62 mm | 80 mm | 70 mm |
| Weight | 2.9 kg | 5.1 kg | 5.1 kg | 7 kg |

DW615



900W plunge router. Two column precision guide for accuracy. Electronic speed control with soft start. 3 stage depth stop adjustment. Supplied with parallel fence, 17mm guide bush, dust extractor kit and 6mm collet.

| | Order Code | Price Each |
|---------|-----------------|------------|
| Voltage | | |
| 230V | 135-3011 | |
| 110V | 135-3012 | |

DW624



1600W plunge router. Routing depth setting with fine adjustment and magnified scale. Dust extraction through the base mounted spout for virtually dust free routing. Supplied with parallel fence, dust extraction adaptor and 30mm guide bush.

| | Order Code | Price Each |
|---------|-----------------|------------|
| Voltage | | |
| 230V | 135-3013 | |

DW625EK



1850W variable speed plunge router. Electronic speed control ensures that the same finish is achieved in all grades of timber, aluminium and plastics since the full wave electronic control ensures that the selected speed is maintained under any load. Soft start eliminates any initial movement that may misalign the cutter. Dust extraction through base for virtually dust free routing. Supplied with parallel fence, dust extraction adaptor, guide bush, collet and carrying case.

| | Order Code | Price Each |
|---------|-----------------|------------|
| Voltage | | |
| 230V | 135-3014 | |
| 110V | 135-3015 | |

DW626



2300W variable speed plunge router. Soft start to eliminate initial movement in start up. Seven stage variable speed selector. Supplied with parallel fence with fine adjustment, dust extraction adaptor, 30mm guide bush, spanner and carry case.

| | Order Code | Price Each |
|---------|-----------------|------------|
| Voltage | | |
| 230V | 135-3016 | |
| 110V | 135-3017 | |

484618