

Immersion Heater Controllers



FST11A SupplyMaster 24 Hour Fused Spur Timeswitch

Digital time control for immersion heaters, storage heaters, convector heaters, water heaters etc.

- Up to 4 ON and OFF programmes per day.
- Permanent OFF and timed outputs available.
- Easy view 24 hour digital clock/timer display.
- Optional 1 or 2 hour boost facility.
- Automatic Summer/Winter time changeover.
- Self-cancelling override.
- Shortest switching time 1 minute.
- Programme advance and review options.
- BS1362 fuse replaceable from front.
- Double pole switch for ease of control.
- Integral memory back up battery retains programmes in event of power failure.
- Fits a single gang wall box min. 25mm deep.
- **Part No. FST11A**

Specification

Timer Mode	24 Hour
Setting Type	Digital
Operating Voltage	230V AC
Switch Rating 230V AC	13A Resistive (3kW)
Operating Temperature	-10 to 40°C
Conforms to Directives	73/23/EEC, 89/336/EEC
Dimensions (mm)	Width 85, Height 85, Depth 38

NOTE: Timeguard has a policy of continuous product development and reserve the right to alter specifications at any time. Therefore, unavoidable differences between product and website specifications may occur, for which liability cannot be accepted by Timeguard.