

## 1 inch Diameter Stainless Steel Compression Load Cell, 0-100 to 0-10,000 LB. Capacities LC304



- ✓ Rugged Heavy Duty Design
- ✓ Built in Load Button for Easy Installation
- ✓ Miniature 1" (25 mm) Diameter and 1" (25 mm) High Case
- ✓ 5-Point Calibration with 59 kOhm Shunt Cal Data

NEWPORT's LC304 Series Load Cell offers the highest output of all miniature load cells. Its small 1" (25 mm) diameter makes it easy to mount in a pocket or on a flat surface. The rugged stainless steel case and high quality construction assure reliability in severe industrial environments.

**The LC304 is also available in metric configurations, with ranges from 0-100 N to 0-50 kN. Please contact our Pressure department for more information.**

Product Selection (Specify Model Number)		
Part Number	Description	Qty.
LC304-50	Compression load cell, 0-50 lb.	
LC304-75	Compression load cell, 0-75 lb.	
LC304-100	Compression load cell, 0-100 lb.	
LC304-500	Compression load cell, 0-500 lb.	
LC304-1K	Compression load cell, 0-1000 lb.	
LC304-3K	Compression load cell, 0-3000 lb.	

LC304-5K	Compression load cell, 0-5000 lb.
LC304-7.5K	Compression load cell, 0-7500 lb.
LC304-10K	Compression load cell, 0-10000 lb.

