

## **SERIES 29**

#### **FEATURES**


- Flush Hole to Prevent Crimping
- Space-Saving <sup>3</sup>/<sub>8</sub>" Diameter or Decorative Flared Skirt
- Dual Mounting Base Accessory



# **DIMENSIONS** In Inches (and millimeters)


### Straight Skirt Style 29-1 BLK and 29-1 RED

Screw post fits  $^3\mbox{/8"}$  (9,53) diameter hole for close spacing.




# **Dual Mounting Base** 29B11-1

For use with 29-1 BLK and 29-1 RED Mounting base is black.



#### Flared Skirt Style 29-3 BLK and 29-3 RED

Screw post fits  $^{1}/_{2}$ " (12,7) diameter hole for wider spacing.



#### **SPECIFICATIONS**

#### Rating Criteria

Rating: At 120 Vdc, 15 Amps continuously, with a maximum temperature rise of 20°C.

Insulation Resistance: Between stud and

mounting panel

For 29-1 styles 120,000 megohms For 29-3 styles 200,000 meghoms **Voltage Breakdown:** Between studs and

mounting panel

For 29-1 styles 1500 Vac For 29-3 styles 3000 Vac

#### **Materials and Finishes**

Metal Parts: Nickel-plated brass

Insulating Materials: Thermoset plastic per

MIL-M-14, Type CFG

#### **Additional Characteristics**

Insulating Washers: Non-turn "D" style Solder Stud: Integral; 2 hex nuts for solder lug connections

Heads: Captive

Cross Hole: Flush to stud extension to eliminate

cutting or crimping wires

Panel Thickness: Up to 3/16" (4,76)

# **ORDERING INFORMATION**

Order using part numbers shown in dimensions.

#### Available from your local Grayhill Distributor.

For prices and discounts, contact a local Sales Office, an authorized local Distributor or Grayhill.