

M12-Splitters/T-Connectors


ASBS 2 M12-S2326 | ASBS 2 M12-S2325 ASBS 2 M12-S1387 | ASBS 2 M12-S3995



M12 Male to 2xM12 Female

Splitter/T-connector, two way, 4-poles with one M12 male connector and two M12 female connectors.


ASBS 2 M12-S2326




M12 Male to 2xM12 Female

Splitter/T-connector, two way, 5-poles with one M12 male connector and two M12 female connectors.


ASBS 2 M12-S2325




ASBS 2 M12-S3187



ASBS 2 M12-S3995



Pin Assignments



Be Certain with Belden



M12-Splitters/T-Connectors

ASBS 2 M12-S2326 | ASBS 2 M12-S2325 | ASBS 2 M12-S3187 | ASBS 2 M12-S3995

Technical Data

Environmental

Degree of protection IP 67 / NEMA 6P

Operating temperature range -15°C (+5°F) / +90°C (+194°F)

Mechanical

Molded body PUR, black Insert PUR, black

Contact Brass, gold over nickel plated

Coupling nut Brass, nickel-plated

0-ring FKM

Electrical

 $\begin{array}{ll} \text{Contact resistance} & \leq 5 \text{ m}\Omega \\ \text{Current rating} & 4 \text{ A} \\ \text{Voltage rating} & 250 \text{ V} \end{array}$

Part Number	Pins	Characteristics
ASBS 2 M12-S2326	4	
ASBS 2 M12-S2325	5	
ASBS 2 M12-S3187	5	
ASBS 2 M12-S3995	5	