

Mini, 7/8" Field Attachable Connectors


RSC 30-RSC 50 | RKC 30-RKC 50



Male, 3-, 4-, and 5-Pole

Field attachable connector, Mini, 7/8" male connector 3-, 4-, and 5-pole with threaded joint, assembling with screw terminals.

RSC 30-RSC 50




- *a O-ring
- *b Pin or screwdriver as assembly tool
- *Ⓜ Contact 1.5 leading



Female, 3-, 4-, and 5-Pole

Field attachable connector, Mini, 7/8" female connector 3-, 4-, and 5-pole with threaded joint, assembling with screw terminals.

RKC 30-RKC 50




- *a O-ring
- *b Pin or screwdriver as assembly tool


Pin Assignments

Mini, 7/8" - Male / Female


3 poles



4 poles



5 poles





Be Certain with Belden

Mini, 7/8" Field Attachable Connectors

RSC 30-RSC 50 | RKC 30-RKC 50

Technical Data

Environmental













Degree of protection IP 67 / NEMA 6P
 Operating temperature range -40°C (-40°F) / +90°C (+194°F)

Mechanical

Housing / Molded body PA
 Insert TPU, self-extinguishing
 Contact CuZn, gold over nickel plated
 Coupling nut Al anodized
 O-ring NBR
 Mode of connection screw terminals
 Connectable conductor max. 1.5 mm²

Electrical

Contact resistance ≤ 5 mΩ
 Nominal current at 40°C 3 poles 12 A
 4-5 poles 9 A
 Nominal voltage 240 V
 Rated voltage 250 V
 Test voltage 3 poles 2.5 kV eff. / 60 s
 4-5 poles 1.5 kV eff. / 60 s
 Insulation resistance > 10⁹ Ω
 Pollution degree 3

Part Number		Pins	Cable Diameter Range	Characteristics
Male	Female			
RSC 30/9	RKC 30/9	3	∅ 6.0 - 8.0 mm	 
RSC 30/11	RKC 30/11		∅ 8.0 - 10.0 mm	 
RSC 40/9	RKC 40/9	4	∅ 6.0 - 8.0 mm	 
RSC 50/9	RKC 50/9	5	∅ 6.0 - 8.0 mm	 
RSC 50/11	RKC 50/11		∅ 8.0 - 10.0 mm	 
RSC 50/13.5	RKC 50/13.5		∅ 10.0 - 12.0 mm	 
RSC 50/16	RKC 50/16		∅ 12.0 - 14.0 mm	