

M12-Receptacle Connectors In Accordance With IEC 61076-2-101


RSF 3...8 | RKF 3...8



Male, 3-, 4-, 5- and 8-Pole

Receptacle, 3-, 4-, 5-, and 8-pole, male, M12 for front mounting, 24 and 22 AWG, panel mount thread PG9.


RSF 3...8



Female, 3-, 4-, 5- and 8-Pole

Receptacle, 3-, 4-, 5-, and 8-pole, female, M12 for front mounting, 24 and 22 AWG, panel mount thread PG9.


RKF 3...8




Pin Assignments

Face Views / M12, Male / Female


3 pole




4 pole



5 pole



8 pole





M12-Receptacle Connectors In Accordance With IEC 61076-2-101

RSF 3...8 | RKF 3...8

Technical Data

Environmental

Degree of protection IP 67 / NEMA 6P
Operating temperature range -40°C (-40°F) / +90°C (+194°F)

Mechanical

Housing Brass, nickel-plated
Insert PUR, black (female)
3-, 4- and 5-Pole: Nylon (male)
8-Pole: PUR, black (male)
Contact Brass, gold over nickel-plated

Electrical

Current rating 3-5 Pole: 4 A
8 Pole: 1.5 A
Voltage rating 3-5 Pole: 250 V
8 Pole: 30 V / 36 V DC

Accessories

Panel nut (RSKF 9)

Part Number		Pins	Characteristics
RSF 3/0.5M	RKF 4-3/0.5M	3	 
RSF 4/0.5M	RKF 4/0.5M	4	 
RSF 5/0.5M	RKF 5/0.5M	5	 
RSF 8/0.5M	RKF 8/0.5M	8	 