



pH • pH

Waterproof, accurate and portable, these handy little pocket meters are true 'go-anywhere' pH testers with replaceable electrodes.

Each meter offers a range of great features.

The difference is in their resolution and accuracy

For 0.1 pH resolution and ±0.1 pH accuracy: select HI 98127

For 0.01 pH resolution and ±0.05 pH accuracy: select HI 98128

Main benefits

- Automatic buffer recognition and calibration
- Robust, replaceable
 electrodes
- Proximity of exposed temperature sensor to pH electrode guarantees greater accuracy in temperature compensated readings
- Calibrate direct into Hanna buffer solution sachets
- Battery % displayed on start up with battery error prevention system (BEPS) to support optimum operation



01525 850855

www.hannainst.co.uk

sales@hannainst.co.uk

Hq



www.hannainst.co.uk

sales@hannainst.co.uk

01525 850855