

Bulk Standard RS-232 Cable, 25 Conductors (12 1/2 Pairs), 1000-ft. (304.8-m)

MFG Part Number: ECN25A-1000



Description

Bulk Standard RS-232 Cable, 25 Conductors (12 1/2 Pairs), 1000-ft. (304.8-m)

Quick Facts

- Unshielded data cable.
- 22 AWG stranded construction.
- Guaranteed for life!

Further Details

- This RS-232 cable can also be used for parallel transmissions up to 20 feet (6 m).

Technical Specifications for Bulk Standard RS-232 Cable, 25 Conductors (12 1/2 Pairs), 1000-ft. (304.8-m):

- **Cable Type** — Gray PVC
- **Capacitance** — 50 pF/ft.
- **Conductor Gauge** — 22 AWG (7 x 30 AWG), stranded
- **Resistance** — Less than 16 ohms/1000 ft.
- **Shield** — None