



ANSI Standard Quick Wire Panel Mounting Socket with Stainless Steel Bracket



'Just push wire in and tighten screw'

About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

- Standard size sockets supplied with stainless steel brackets
- Easy 'jab-in' connection for rapid termination, just push wire in and tighten screw
- Intended for use in more industrial processes but can be used in all applications as desired
- Available in Thermocouple types K, J, T
- For Types K, J, T contacts are made from true Thermocouple alloys
- Colour coded in accordance with ANSI specification
- Maximum continuous operating temperature 220 deg°C

T/C Type	Colour Code (ANSI)	+Positive (alloy type)	-Negative (alloy type)	Labfacility Code	Farnell Code
K	Yellow	+Nickel Chromium	-Nickel Alloy	AS-K-SSPFQ	234-7163
J	Black	+Iron	-Copper Nickel	AS-J-SSPFQ	234-7162
T	Blue	+Copper	-Copper Nickel	AS-T-SSPFQ	234-7164

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com