



LRM-2521

Professional 10 x 2.5" TFT LCD Rackmount Monitor. Suitable for surveillance systems, VJ Monitor or other multimedia purposes.

10 X 2.5" LCD Screens
1 Video BNC Inputs
1 Video BNC Output
Tilt adjustment for optimum viewing angle
Heavy duty metal housing
Universal power supply

Display: 2.5" TFT LCD
Display Area: 50.4 X 37.8 mm
Resolution: 960 X 240 pixels
Brightness: 230 cd/m²
Contrast Ratio: 300:1
Viewing angle: L/R 50° Top: 20° Down 70°

Video input specification: 1 BNC video inputs per screen
Video output specification: 1 BNC video outputs per screen

Power Source: 12VDC, 3.3A
Power consumption: 450 mA, 5W Max.
AC/DC Power Adapter Input: 100V to 220V AC
Weight: 4 KG
Dimensions: 49(W) x 6.4(D) x 13.2(H) cm
Included: PSU, IEC Cable and Manual.