



DCD985M2

18V XRP XR Li-Ion Cordless Hammer Drill Driver

Selling Proposition

- Latest generation 18V XR Li-Ion XRP hammer drill driver featuring NEW XR 4.0Ah Li-Ion battery technology
- Tough 3 speed all metal transmission for increased runtime and longer tool life
- 22 position adjustable torque control for optimised precision when screwdriving
- 13 mm ratcheting keyless chuck with automatic spindle lock for fast bit changes
- Efficient intelligent trigger allowing total control over all applications
- Bright white LED with delay feature for improved visibility and flashlight functionality

Standard Equipment

- Multi position side handle
- Multi-voltage charger
- 2 slide batteries
- Heavy duty kit box

Warranty Specifications

- 3 Year Limited Warranty
- 30 Day Money Back Guarantee
- 1 Year Free Service Contract

Specifications	
Battery chemistry	XR Li-Ion
Voltage	18 V
Battery Capacity	4.0 Ah
Max Torque	80 Nm
Power Output	500 Watts
No Load Speed	0-575/1,350/2,000 rpm
Beats per Minute	0-9,755/22,950/34,000 bpm
Chuck Capacity	1.5-13 mm