



DCG412M2

18V XR Li-Ion Grinder

Selling Proposition

- Latest generation 18V XR Li-Ion premium Grinder featuring NEW XR 4.0Ah Li-Ion battery technology
- Part of the intelligent XR Lithium Ion Series designed for efficiency and making applications faster
- Powerful & Highly Efficient PM58 DEWALT fan cooled motor with replaceable brushes, delivers up to 7000 rotations per minute for fast cutting and grinding applications
- Steel cut spiral bevel gears provide highest level of durability and low vibration, increasing user productivity
- Low profile jam pot gear case improves gear durability and ergonomics
- Intelligent trigger & lock-off switch for enhanced work safety & control

Standard Equipment

- 2 position side handle
- Keyless protective guard
- Blade Wrench
- Multi-voltage charger
- 2 slide batteries

Warranty Specifications

- 3 Year Limited Warranty
- 30 Day No Risk Satisfaction Guarantee
- 1 Year Free Service Contract

Specifications

Voltage	18 V
Battery Capacity	Li-Ion 4.0 Ah
Max. Disc Diameter	125 mm
Power Output	405 Watts
No Load Speed	7000 rpm
Spindle Thread	M14
Weight	2.9 kg
Length	400 mm