

ACS, Incorporated

Home About Us Contact

630.325.2700 ..| 800.248.5391..



**Business Two-Way Radios**

- CLP Series - UHF
- CLS Series - UHF
- RDX Series - UHF
- RDX Series - VHF
- DTR Series- Digital UHF

**Industrial Cordless Phone with Built-in Two-Way Radio**

CLS1450cB

**Discontinued Business Two-Way Radios**

- AX Series
- XTN Series

**Business Two-Way Radio Accessories**

- CLP Series Accessories
- CLS Series Accessories
- CLS1450cB Accessories
- RDX Series Accessories
- DTR Series Accessories
- AX Series Accessories
- XTN Series Accessories

Antennas

Audio and Headsets

Batteries

Chargers

Holsters and Cases

**Wireless Callboxes**

Outdoor UHF or VHF

**Recreational FRS-GMRS**

Recreational Walkie-Talkies

Recreational Accessories

**Facts About Business Two-Way Radios**

- Two-Way Radio Basics
- Inexpensive FRS/GMRS Walkie-Talkies
- Return On Investment
- Range and Coverage
- Business Frequencies
- Interference Eliminator Codes

**Business Two-Way Radio Applications**

Who is using two-way radios?

**FCC License Information**

- FCC License
- FCC Narrowbanding

**Repair and Warranty**

Repair and Warranty

**Customer Programming Software**

- CLP Software
- RDX Software
- DTR Software

**Literature**

**UHF - RDX Series Business Two-Way Radios**



**Compact, Rugged & Durable**

The Motorola RDX Series™ provides your business with a competitive communications edge, enhancing employee efficiency and overall profitability. With exceptional audio quality and a rugged design, the RDX Series helps keep your operations on schedule, maximize job-shift productivity, enhance security and increase overall customer satisfaction. Compatible with other radios operating on the same frequency and code, the versatile RDX2020 also has a full complement of accessories for customizing the radio to suit your needs.

**RDU2020, RDU2080d Series**

- 2 Watt transmit power
- 2 Channel (RDU2020) and 8 Channel (RDU2080d) models
- 89 Built-in user changeable UHF frequencies(12.5 kHz narrowband capable)
- Interference Eliminator with 122 Codes (83 digital DPL, 39 analog PL)
- Channel scan
- Audio accessory jack – use with headsets and speaker mic
- VOX Voice activated transmit with select audio accessories
- Voice Scramble option for added privacy and security
- Robust 2000 mw audio output, 30% louder than other models
- Speaker has low magnetic field to greatly reduce attraction of metal shavings
- Free Custom Programming Software option (requires RKN4155 cable)
- Meets Military Standards for high resistance to dust, moisture, shock, vibration

**RDU2080d Features**

- LCD Display shows channel or workgroup, provides quick access to frequency & code settings and battery status
- Channel Alias – Custom name each channel for quick identification
- Meets Military Standards for high resistance to dust, moisture, shock, vibration

**Includes**

- Li-Ion Battery, Standard Capacity 1100 mAh, up to 12 hrs (AA Capable emergency power)
- 7 Hour desktop charger
- Heavy duty spring action belt clip

**RDU4100, RDU4160d Series**

- 4 Watt Transmit Power
- 10 Channel (RDU4100) and 16 Channel (RDU4160d) models
- 89 Built-in user changeable UHF frequencies or dealer programmable to frequencies 438 – 470 MHz (12.5 kHz narrowband capable)
- Interference Eliminator with 122 Codes (83 digital DPL, 39 analog PL)
- Channel scan
- Audio accessory jack – use with headsets and speaker mic
- VOX Voice activated transmit with select audio accessories
- Voice Scramble option for added privacy and security
- Robust 2000 mw audio output, 30% louder than other models
- Speaker has low magnetic field to greatly reduce attraction of metal shavings

End User 4 page Brochure  
Full Line Catalog MSRP  
Reduce Labor Brochure  
Questions to Ask End User  
Operational Manuals  
Promotions

**Motorola Logo Guidelines**

Motorola Logos

- Free Custom Programming Software option (requires RKN4155 cable)
- Compatible with repeater/range extenders and base stations
- Meets Military Standards for high resistance to dust, moisture, shock, vibration

**RDU4160d Special Features**

- LCD Display shows channel or work group, provides quick access to frequency, code settings and battery status
- Channel Alias – Custom name each channel for quick identification
- Meets Military Standards for high resistance to dust, moisture, shock, vibration

**Includes**

- Li-Ion Battery, Ultra Capacity 2400 mAh, up to 18.5 hrs (AA Capable emergency power)
- 12 Hour desktop charger
- Heavy duty spring action belt clip

**> RDX Programming Software**

- Customize your settings to fit your business applications
- Add or remove groups or contacts
- Prevent users from changing settings
- Quickly copy settings from one radio to another for add-ons or replacements
- Personalize the name of the radio
- Personalize the name of each group

[Home](#) | [Facts](#) | [Application](#) | [Warranty](#) | [Literature](#)

© 2007-2013 acsspirit.com - All rights reserved - No duplication of any type is permitted without written permission from ACS, Incorporated