GRM1555C1H101JD01#

"#" indicates a package specification code.








< List of part numbers with package codes >

GRM1555C1H101JD01D , GRM1555C1H101JD01W , GRM1555C1H101JD01J

Shape





L size 1.0 ± 0.05 mm W size 0.5 ± 0.05 mm 0.5 ± 0.05 mm T size 0.15 to 0.35mm External terminal width e 0.3mm min. Distance between external terminals g Size code in mm(inch) 1005 (0402)

Specifications

Capacitance 100pF ± 5% 50Vdc Rated voltage COG(EIA) Temperature characteristics (complied standard) 0 ± 30ppm/ Temperature coefficient Temperature range of temperature characteristics 25 to 125 Operating temperature range -55 to 125

References

	Packaging	Specifications	Minimum quantity
D	180mm Paper taping	10000	
J	330mm Paper taping	50000	
W	180mm Paper taping (W8P1*) * Width : 8mm, Pocket pitch : 1mm	20000	
			1 of 1

Attention

- 1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it 's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



muRata Murata Manufacturing Co., Ltd.

URL: http://www.murata.co.jp/

Last updated: 2013/09/23