



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: PS7224-20HW

24-outlet Vertical Power Strip with Hardwire Input and 20A Circuit Breaker

Highlights

- AC input hardwired via knockout on unit
- 24 outlets
- Ideal for applications requiring permanent installation



Description

Tripp Lite's PS7224-20HW Power Strip offers 20 amp multi-outlet AC power distribution in a convenient 72 inch hardwire cabinet. Includes knockout panels to accept 3/4 in. conduit fittings for hardwire installation and 24 output receptacles with 2.795 inch center-to-center spacing. Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications.

INPUT/OUTPUT: Input: Hard-wire access via knockout panels that accept 3/4 inch conduit fittings

Output: 24 outlets total, 2 NEMA 5-15/20R (20A) and 22 NEMA 5-15R (15A)

ELECTRICAL: 120V AC, 50/60Hz, 20A (no circuit breaker)

FORMAT: 72 inch strip format with 24 outlets

Applications

- Offers multiple outlet power distribution for a variety of applications, including office, workbench, industrial, networking, telecom and more.

Package Includes

- PS7224-20HW
- Instruction manual

Features

- Versatile all-metal 72 inch format with outlets arranged in a single row
- Knockout panels for 3/4 inch conduit fittings allow permanent hardwire installation
- Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications
- 24 outlets total, 2 NEMA 5-15/20R (20A) and 22 NEMA 5-15R (15A)
- 20 amp electrical capacity
- 120V AC, 50/60Hz electrical compatibility

Specifications

OVERVIEW

Intended Application	Home/Office
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	2400
Circuit Breaker (amps)	20
Outlet quantity / type	22 NEMA 5-15R & 2 NEMA 5-15/20R
Outlet spacing	2.795 in.
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	20A 120V
Input connection type	Hardwire
Voltage compatibility (VAC)	120
PHYSICAL	
Unit Dimensions (HWD/in)	72 x 1.5 x 1.5
Unit Dimensions (HWD/cm)	182.88 x 3.8 x 3.8
Material of construction	Metal
Integrated keyhole mounting tabs	Mount through housing supports bolt down installation to a variety of flat surfaces
Receptacle Color	Almond
Style	Bench/Cabinet Mount
Outlets center to center measurement	101.60mm
CERTIFICATIONS	
cUL / CSA (Canada)	cUL
Approvals	UL
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=201.

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.