



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: TLM626NS

Power It! Safety Power Strip with 6 Outlets and 6-ft. Cord



Highlights

- 6 outlets (including transformer outlets and 4 safety covers)
- 6 ft. cord
- Rugged metal case

Description

This Tripp Lite power strip is designed to safely distribute power to connected equipment in harsh environments. It provides a convenient source for multiple outlets wherever they're needed. 6 outlets distribute AC power to a wide range of power tools, pumps, air compressors and more. Convenient transformer outlets accommodate multiple transformers without blocking other outlets. A 6 ft. grounded cord with integrated cord clip reaches distant outlets. A lighted on/off switch with integrated circuit breaker provides power control over connected equipment. Breaker protects against dangerous system overload. 4 safety covers shield unused outlets from debris and accidental contact. A rugged metal case stands up to the harshest environments. Integrated keyhole slots on bottom panel provide convenient wall/desk mounting. Its bright yellow color alerts you and others that power cords and tools are in use.

Applications

- Industrial
- Automotive
- Factory
- Hardware

Package Includes

- TLM626NS Safety Power Strip
- 4 safety covers
- Owner's manual

Features

- 6 outlets distribute AC power to a wide range of power tools, pumps, air compressors and more.
- Convenient transformer outlets
- A 6 ft. grounded cord with integrated cord clip reaches distant outlets.
- A lighted on/off switch with integrated circuit breaker provides power control over connected equipment. Breaker protects against dangerous system overload.
- 4 safety covers shield unused outlets from debris and accidental contact.
- A rugged metal case stands up to the harshest environments.
- Integrated keyhole slots on bottom panel provide convenient wall/desk mounting
- Its bright yellow color alerts you and others that power cords and tools are in use.

- OSHA color guidelines, outlined in Document 1910.145, alert users to hazardous situations, which may cause minor or moderate injury. This Tripp Lite product complies with those guidelines.

Specifications

OVERVIEW	
Intended Application	Safety; Industrial/Factory Floor
OUTPUT	
Frequency compatibility	60 Hz
Circuit Breaker (amps)	15
Overload protection	Combo power switch and circuit breaker
Outlet quantity / type	6 NEMA 5-15R
Transformer accommodation	Yes (2)
Outlet safety covers	Yes (4)
Outlet orientation	Single row
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V, 15A
Input connection type	NEMA 5-15P
Input plug features	Integrated cord clip
Input cord length (ft.)	6
Input cord length (m)	1.83
Input cord gauge, type	14 gauge, SJT
Voltage compatibility (VAC)	120
PHYSICAL	
Shipping Dimensions (HWD/in)	13.61 x 4.97 x 2.01
Shipping Dimensions (HWD/cm)	34.57 x 12.62 x 5.11
Shipping weight (lbs)	1.58
Shipping weight (kg)	0.72
Unit Dimensions (HWD/in)	12.23 x 2.30 x 1.28
Unit Dimensions (HWD/cm)	31.06 x 5.84 x 3.25
Unit weight (lbs)	1.34
Unit weight (kg)	0.61
Material of construction	All-metal
Integrated keyhole mounting tabs	Yes

Receptacle Color	black
AC line cord color	yellow
Style	Strip
Outlets center to center measurement	Distance between standard outlets = 30.40mm; Distance between standard and transformer outlets = 45mm
Keyhole slot center to center measurement	225mm
CERTIFICATIONS	
Approvals	cULus, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=3680.

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.