




RED INDICATES ORIGINAL




SCALE 2



REVISIONS				305-0013	SH 1
REV	ECO NO.	DESCRIPTION	DWN	APPROVED	DATE
L	11328	REDRAWN IN PRO/E WITH CHANGE: SH. 12 "D" FLAT PIN DEPTH WAS .200 B/M P/N 8-2149-3 WAS 8-2149-2	SAC	<i>bu: FO</i>	12/21/95



INCH	MM
.005	0.13
.015	0.38
.030	0.76
.036	0.91
.062	1.57
.125	3.18
.187	4.75
.190	4.83
.386	9.65
.439	11.15
.443	11.25
.487	12.37
.500	12.70
.562	14.27
.600	15.24
.892	22.66
1.122	28.50



RECOMMENDED
PANEL CUTOUT
SCALE 2/1

4. MAX PANEL THK .125

3. SOCKET CONTACT CONCENTRIC TWINAX/
TRIAx TRT SOLDER POT BULKHEAD
MOUNT RECEPTACLE

2. FINISH: TES-1A (NICKEL)

1. ALL DIM ARE IN INCHES

QTY	DESCRIPTION		PART NUMBER		ITEM
TOL UNLESS SPECIFIED	TROMPETER ELECTRONICS, INC. ©		BJ377		
.XX ± .005	DWG	SAC	12-6-95	MATERIAL	CODE IDENT
.XXX ± .005	CHK	<i>DM</i>	12-14-95	—	14949
.XXXX ± .005	ENGR	—	—	DRAWING NO.	305-0013
ANGLE ±	APPR	<i>FO</i>	12/21/95	DATE	11-12-68
NEXT ASSY	SCALE 4/1		SHEET 1C		REV L