

(P/N° 332-6238)

brother.**NEW PRODUCT
SPECIFICATION****Model Name****PT-2400****P-Touch Labelling Machine****HARDWARE**

Housing Design
Housing Colour
Keyboard
Number of Keys
Cutter
Power

Small Desktop Type
Dark Grey
QWERTY
51 Keys
Yes - Auto
8 x AA Batteries (Included)
Optional AC Adaptor Type H
12 Characters x 2 Lines
PT-350 Labelling Machine
12mm Black on White Tape, User's Manual
6 x AA Batteries, Tape Separator

LCD
Carton Contents

Options
Tape Type

Carrying Case
TZ Tapes
Laminated, Non-Laminated, Fabric, Stamp
6, 9, 12, 18, 24mm
128dot (available 96 dot)/180dpi
10mm/Sec

Tape Size
Print Head
Print Speed

SOFTWARE

Built-In Fonts

Helsinki, Brussels, US, Los Angeles,
San Diego, Florida, Belgium, Istanbul
197 Characters & Symbols

Number of Character & Symbols
Max Print Height
Character Size (Point)
Text Buffer
File Memory
Print Styles

18.1mm
Auto, 6, 9, 12, 24, 36, 48, Big
Approx 250 Characters
Approx 1,000 Characters

Multi-Line
Multi-Block
Framing & Fill Pattern

Normal, Outline, Shadow, Bold, Italic, Italic & Outline,
Italic & Shadow, Italic & Bold

Barcode

Up to 7 Lines
Up to 5 Blocks
Square, Round, Fill Pattern (dot), Fill Pattern (Diamond),
Fill Pattern (Slant), Telephone, Dog, Cat, Hands
Candy, Banner, Aeroplane, Vine, Flowers
CODE39, I-2/5, EAN8, EAN13, UPC-A, UPC-E,
CODABAR, Code 128, EAN128

Underline
Tape Margin Settings

Underline, Strike Out
None (4mm), Narrow (8mm), Medium (12mm),
Full (25mm)

Copy Printing
Horizontal Alignment
Vertical Alignment
Mirror Printing
Text Insert
Vertical Printing
Split Printing
Stamp Software

1 - 99
Left (Default), Right, Centre
Centre Only
Yes
Yes
Yes
No
Yes

Numbering
Auto Format
Tab Function
Auto Power Off
Multi-Colour Software
Label Length Setting

OTHERS

Machine Dimensions (WxDxH)
Weight
Barcode

1 - 99
30 Kinds
Yes
Yes
No
Auto, 40mm - 300mm

188mm x 234mm x 65mm
850g (Excluding Batteries)
4977766527217