

Model #: TLP808TEL

8-outlet, 8-ft cord, 2160 joule with modem/fax protection - Protect It! Surge Suppressor



Highlights

- 8 outlets / 8-ft. cord
- 2160 joule rating
- Modem/fax surge protection
- \$150,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

Description

Tripp Lite's TLP808TEL surge suppressor has 8 outlets, an 8-ft. cord with a space-saving right-angle plug, and diagnostic LEDs. The unit has a surge suppression rating of 2160 joules to handle the strongest surges. Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment. \$150,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

Applications

• Ideal for home computers and other important electrical equipment

Package Includes

- TLP808TEL
- 6-ft. telephone cord
- Instruction manual with warranty information

Features

- 2160 joules AC surge suppression shields equipment from the strongest surges and line noise
- 8 AC outlets with room for 3 transformer plugs without blocking outlets covers computers and all peripherals
- . Long 8 foot AC line cable with space-saving angle input plug conveniently reaches distant outlets
- built-in RJ11 jacks (1in/2 out) prevent surges from damaging your modem/fax/phone equipment
- Lighted power switch with integrated 15 amp circuit breaker offers power control and overload protection
- Integrated child-safety sliding outlet covers safely seal off all unused outlets
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- Attractive white suppressor housing with keyhole mounting tabs allow versatile placement options
- \$150,000 Ultimate Lifetime Insurance (USA and Canada Only)

Specifications

OVERVIEW	
Intended Application	Home/Office
OUTPUT	

Frequency compatibility	50 / 60 Hz	
Output watts	1800W	
Circuit Breaker (amps)	15	
Outlet quantity / type	8 NEMA 5-15R	
Transformer accommodation	Supports 3 large transformer plug accessories without covering remaining outlets, accepts up to 6 transformers total	
Outlet safety covers	Includes built-in sliding outlet safety covers	
Outlet orientation	Single row of 5, plus a second row of 3 for transformer accommodation	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	120V (110-125V)	
Input connection type	NEMA 5-15P	
Input plug features	Space-saving right angle input plug	
Input cord length (ft.)	8	
Input cord length (m)	2.4	
Input cord gauge, type	14 gauge, SJT	
Voltage compatibility (VAC)	120	
Maximum Surge Amps	144000	
LEDS ALARMS & SWITCHES		
Switches	Combination AC circuit breaker and 2-position red illuminated on/off power switch	
Diagnostic LEDs	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status	
SURGE / NOISE SUPPRESSION		
AC suppression joule rating	2160	
AC suppression response time	< 1 ns	
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression	
Clamping voltage (RMS)	150	
UL1449 let through rating	330/400/400	
EMI / RFI filtering	Up to 40 dB	
DATALINE SURGE SUPPRESSION		
Telephone/DSL Protection Details	1 line	
Cable (Coax) Protection	No	
Network (Ethernet) Protection	No	
PHYSICAL		

Shipping Dimensions (HWD/in)	11.41 x 8.66 x 2.04	
Shipping Dimensions (HWD/cm)	28.98 x 22.00 x 5.18	
Shipping weight (lbs)	2.06	
Shipping weight (kg)	0.93	
Unit Dimensions (HWD/in)	4.86 x 9.55 x 1.51	
Unit Dimensions (HWD/cm)	12.34 x 24.26 x 3.84	
Unit weight (lbs)	1.89	
Unit weight (kg)	0.86	
Material of construction	Plastic	
Integrated keyhole mounting tabs	Keyhole mounting slots enable wall mounting	
Housing Color	Light Gray	
Receptacle Color	Light Gray	
AC line cord color	Light Gray	
Style	Strip	
Keyhole slot center to center measurement	Distance between horizontal slots = 75mm; Distance between vertical slots = 41.6mm	
SPECIAL FEATURES		
Additional Information	Pair of phone line output jacks serve as a line splitter to enable the protection of two devices sharing a single dialup phone line	
Right-Angle Plug	Yes	
CERTIFICATIONS		
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION	
UL1363 (Power Tap)	UL1363	
UL497A (Communications)	UL497A	
FCC Part 68 (Communications)	FCC Part 68	
cUL / CSA (Canada)	cUL	
Industry Canada (Communications)	Industry Canada	
Approvals	Exceeds IEEE 587 category A&B specifications	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 Ultimate Lifetime Insurance	

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModeIID=141.

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.