PRODUCT DATASHEET

LED Inspection Light



HARDCASED

DURABLE

Survives 1-meter drop test



TUFPL22PH

Big light in a small package, the Energizer® Hardcase Professional® LED Inspection Light is ready to take on the toughest jobs. Designed to fit easily in a pocket or in the included belt holster, this light is easy to keep at hand. In addition it is water resistant and can withstand a 1-meter drop, making it ideal for even the roughest conditions on the job. Backed by a lifetime warranty, the TUFPL22PH is The Toughest Flashlight You'll Ever Need™.

WATER RESISTANT

- Meets IEC 60529 IPX4 standards
- Continues to operate after exposure to splashing water from all directions



BRIGHT

• White LED provides 40 lumens of light





HANDY

- Easy to use push button switch
- Slim, tapered design fits easily in pockets



Before Using Your Flashlight:

Please read all instructions and cautionary markings on the package and light

Product Detail:

Designation: Energizer Hard Case Professional

LED Inspection Light

Model: TUFPL22PH

Color: Black and Gray **Power Source:** Two "AAA"

ANSI/NEDA: 24 Series

Lamp: 1 White CREE® XRC LED

Lamp Life (hr): Lifetime

Lamp Output (lumens): 40
Beam Distance (m): 76

Peak Beam Intensity (cd): 1,480

Run Time (h:mm): 1:15

Typical Weight: 53.1 grams


without batteries

Dimensions (mm): 149 x 24

Performance:

Run Time

Continuous Drain to End of Useable Light (21°C)



Battery Type

Tested according to ANSI/NEMA FL 1 Standards.

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication

Contents herein do not constitute a warranty © Energizer / All Rights Reserved

