

# HU361

## SWITCH NOT FUSIBLE HD 600V 30A 3P NEMA1



by Schneider Electric

### Main

|                                |   |
|--------------------------------|---|
| Commercial Status              | Commercialised                            |
| Product or component type      | Single Throw Safety Switch                |
| [In] rated current             | 30 A                                      |
| Product certifications         | UL listed                                 |
| NEMA degree of protection      | NEMA 1 steel                              |
| Device composition             | None                                      |
| Disconnecter device type       | Non-fusible disconnect                    |
| Short-circuit current          | 200 kA maximum                            |
| Device mounting                | Surface                                   |
| Number of poles                | 3   |
| Electrical connection          | Lugs                                      |
| Series name                    | Heavy duty                                |
| [Ue] rated operational voltage | 600 V AC/DC                               |
| AWG gauge                      | 14...6 AWG copper<br>12...6 AWG aluminium |

### Ordering and shipping details

|                       |   |
|-----------------------|---|
| Category              | 00008 - H&HU, 2&3P, N1, 30-200A                   |
| Discount Schedule     | DE1   |
| GTIN                  | 00785901505723                                    |
| Nbr. of units in pkg. | 1   |
| Package weight(Lbs)   | 7.64  |
| Product availability  | Stock - Normally stocked in distribution facility |
| Returnability         | Y   |
| Country of origin     | US  |

### Offer Sustainability

|                          |   |
|--------------------------|---|
| Sustainable offer status | Not Green Premium product                         |
| RoHS                     | Will be Compliant on 3Q2014                       |
| REACH                    | Reference not containing SVHC above the threshold |

### Contractual warranty

|        |           |
|--------|-----------|
| Period | 18 months |
|--------|-----------|