



Overview

Countersunk Head 60 Screws - PoziDriv®

Three-lobed threadform

Imperial dimensions

Materials and Finishes

Hardened steel/Zinc & clear de-embrittled

Stainless Steel/Self colour

Please note: Not all sizes stated are available from stock, please enquire for availability.

Note: Due to the fact that fastening applications differ greatly, the below information is for guidance only and is correct to the best of our knowledge. The customer must satisfy themselves with the performance of the fastener and validity of the data. TR Fastenings will not be held responsible for any failure that may occur from the use of this information

Dimension Data

Size	No.2 (28)	No.4 (20)	No.6 (19)	No.8 (16)	No.10 (14)
D dia	0.089	0.123	0.143	0.179	0.208
C dia	0.092	0.127	0.147	0.185	0.212
d1	0.172	0.225	0.279	0.332	0.385
K	0.051	0.067	0.083	0.1	0.116
Recess No.	1	1	2	2	2

C dimension measured with a tri-fluted micrometer

D diameter measured with a standard micrometer

Values in () denote threads per inch

Stainless Steel - all sizes non-preferred - Please enquire for availability

Part number	Finish	Length	Material	Thread
W/N6/0.375/KRST60/TC1D	Zinc Trivalent Clear De-embrittled	9.5mm (3/8")	Steel	3.5mm (No.6)