SUPPLIED ON TAPE AND REEL

SUPPLIED ON TAPE AND REEL

- Manufactured using flat wire to provide a large mounting surface area
- Ideal for use with miniature probes, clips, and hooks
- · Efficient, safe, board level testing
- Ultra low profile, ideally suited for advanced surface mount printed circuit board applications
- · Designed for long life and durability

#### **SPECIFICATIONS**

#### **Contact Material:**

.010 (.25) Phosphor Bronze Contact Finish: Silver Plate

Tape Material: 8mm wide; 4mm pitch; conductive polycarbonate carrier tape meets ANSI/EIA-481 standard

**CAT. NO. 5015** - 1000 pieces per reel

# .105 [2.7] .040 [1.00] .040 [1.00] .060 [1.50]

#### Pad Layout







**CAT. NO. 5017** - 5000 pieces per reel

#### MINIATURE


- Ideal for use with most standard probes, clips and hooks\$
- · Efficient, safe, board level testing
- · Unique design provides exceptional strength and durability
- Simplifies testing on dense SMT circuit boards


#### **SPECIFICATIONS**


#### **Contact Material:**

.015 (.38) Phosphor Bronze Contact Finish: Silver Plate

Tape Material: 12mm wide; 4mm pitch; conductive polycarbonate carrier tape meets ANSI/EIA-481 standard











**CAT. NO. 5019** - 1000 pieces per reel **CAT. NO. 5029** - 5000 pieces per reel

- · Ideal for use with standard probes, clips and hooks
- · Efficient, safe, board level testing
- · Unique design provides exceptional strength and durability
- · Simplifies testing on dense SMT circuit boards

# COMPACT

#### SUPPLIED ON TAPE AND REEL







#### **SPECIFICATIONS Contact Material:**

.015 (.38) Phosphor Bronze Contact Finish: Silver Plate

Tape Material: 12mm wide; 4mm pitch; conductive polycarbonate carrier tape meets ANSI/EIA-481 standard

**CAT. NO. 5016** - 1000 pieces per reel

**CAT. NO. 5018** - 5000 pieces per reel

# **ALLIGATOR CLIPS**

#### **SMALL CLIP**

- · Solder Connection with Strain Relief
  - Insulated or Non-Insulated





CAT. NO.	INSULATOR COLOR
5033	NONE
5034	RED
5035	BLACK
5036	GREEN
5037	YELLOW

#### JAW SPREAD .236 (6.0) max.

MATERIAL: Clip: Steel, Nickel Plate Insulator: Vinyl

#### **MEDIUM CLIP**

• Solder Connection with Strain Relief · Insulated or Non-Insulated



70	.335 (8.5)
	.335 (6.5)
1.40 (35.5)	

CAT. NO.	INSULATOR Color
5038	NONE
5039	RED
5040	BLACK


## JAW SPREAD .236 (6.0) max.

# MATERIAL:

Clip: Steel, Nickel Plate Insulator: Vinyl

### **LARGE CLIP**

- Solder Connection or Screw Connection (Barrel Accepts Wire or Standard Banana Plugs)
  - · Insulated or Non-Insulated



CAT. NO.	INSULATOR COLOR
5044	NONE
5045	RED
5046	BLACK
5048	SCREW INSTALLED

# JAW SPREAD .315 (8.0) max.

# **MATERIAL:**

Clip: Steel, Nickel Plate Insulator: Vinvl

Tel (718) 956-8900 • Fax (718) 956-9040

(800) 221-5510 • kec@keyelco.com