

**THB.405.3KIT**

TeePlug 3 pole in-line Plug and Socket, Screw terminal 7mm to 14mm cable diameter, 4 mm max conductor size IP68 25A 400V 2 cable entry, retail pack


**PRODUCT SPECIFICATIONS**

Temperature "T" rating	T125
Minimum cable diameter (mm)	7
Maximum cable diameter (mm)	14
Fixing system	Cable
Cable entries	2
Number of poles	3
Terminal type	Screw
Body material	PA66
Max conductor size (Sq mm)	4
Max current (A)	25
Max voltage (V)	400
Minimum temp rating °C	-40
Max temp rating °C	125
IP rating	68