



Sample photo

Order symbol: UL CAB PC 303018 G
Product nbr: 8143340
Description: UL Cabinet, PC
Remarks: Latches on the long side, smooth

EAN: 6418074053923
El. number:
Finland:
Denmark: 8212034073
Italy: 7821025U
Norway:

Including: Cabinet base, door with EPDM gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:	Length	Width	Height
mm:	300	300	180
inch:	11.8	11.8	7.1

Materials:	
Material:	Polycarbonate
Base colour:	RAL 7035
Cover colour:	RAL 7035
Gasket material:	EPDM

Temperatures:	
Short term:	-40 ... 120 °C
Continuous:	-40 ... 80 °C
Short term:	-40 ... 250 °F
Continuous:	-40 ... 175 °F

Accessories:

Rating:
Ingress Protection (EN 60529): IP 65
Impact Resistance (EN 62262): IK 08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): Yes
UV resistance: UL 508
Flammability Rating (UL 746 C 5): UL 746C 5V
Glow Wire Test (IEC 695-2-1) °C: 960
UL Type: UL TYPE 1, 4, 4X, 12, 13

Certificates:
Germanischer Lloyd (GL)
Underwriters Laboratories
Fimko
Lloyds Register of Shipping (LR)
Europe EN 62208: 2003
UL Canada
Gost R

