




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORPORATION.

PANDUIT PART NUMBER	DIMENSIONS				MAXIMUM CABLE DIA. in. (mm)	ADHESIVE BACKING	WEIGHT lbs/100 pcs (g)/100 pcs
	A	B	C	D			
ACC62-A	1.12 (28.5)	1.24 (31.4)	.73 (18.5)	0.65 (16.5) (REF)	0.62 (15.7)	RUBBER	0.96 (437)
ACC62-AT						ACRYLIC	
ACC62-AV						HIGH BOND ACRYLIC	



NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.

CAD FILENAME/LAYERS		G03597BD_DC_GB0239BB/00C	
PANDUIT CORP.		TINLEY PARK, ILLINOIS	
ACC62-A, ACC62-AT, ACC62-AV ADHESIVE CORD CLIP			
DRAWN BY JRL		MAT'L: NYLON 6/6	
DATE 9-11-92		SCALE FULL	
CHK'D KLN		DRAWING NO. GB0239BB	
DESCRIPTION		DWG SIZE A	

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
00C	11-6-09	TMSA	SMY	ADDED PART NUMBER ACC62-AV	GB0239BB	00C	KLN	
00B	7/9/08	DJSM		REVISED AND RE-RELEASED TO TEAMCENTER REV HISTORY; TABULARIZED DIMS; REMOVED .86 AND .49 DIMS; REVISED .63 DIM TO INCLUDE TAPE; .73 WAS .74; REMOVED TAPE, APPLICATION, AND WARRANTY NOTES	GB0239BB	00B		
3	7/18/00	JAD		DIMENSIONS, .63, .86, & .49 WERE CHANGED TO REF DIMENSIONS	GB0239BB	3		

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)
(.XX) ±0.02 (.5) ANGLES ±5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION