

Solid rechargeable portable searchlight
with secure dependable technology
2 year warranty

- halogen rechargeable handlamp with
dimmer, wandholder and
charging electronic
- with mains failure electronics
 - dimmer from 0 to 100 %
 - beam 1500 m
- operating time depending on
- dimmer position 30-120 Min.
 - 20 Watt
 - halogen lamp 6V/3,3A
 - Socket G 4
- with mains failure electronics, the
accumulator searchlight switches
on automatically and therefore
serves as an emergency res. safety
light
- incl. carrying strip

Tech. specs:	Leuchtmittel/ bulb: HA 6V/ 20W/ G4 Leuchtweite/ beam: 1500m Leuchtdauer/ operating time: 30-120min
Sizes:	L 280mm, Kopf/Header Diameter 110mm
Weight:	600g (nur Lampe/Searchlight only)

order no. Euro version:	5102042
order no. USA / Canada version:	N/A
order no. UK version:	5502036
order no. Australia version:	N/A
order no. Japan version:	N/A
order no. South Africa version:	N/A

Table of charging times (with empty batteries)