


## VECTORBORD®PLUGBORD™ PART NO. : 3662-2



### Description :

- 4.5" X 6.5" X 0.062, Hole Dia.: 0.042", Grid: 0.100" X 0.100"
- Plated Contacts Only
- Unrestricted component placement over entire board surface
- Row and column legends provided
- Layout paper and instructions included..... [Layout Paper\(PDF\)](#)

<b>Circuit Pattern :</b>	<b>Plated Contacts Only</b>
<b>Contacts :</b>	<b>22/44 @ 0.156" Centers Ni / Gold</b>
<b>16 Pin DIP Capacity :</b>	<b>25</b>
<b>Hole Diameter :</b>	<b>0.042" { 1.0668 mm }</b>
<b>Grid :</b>	<b>0.100" X 0.100" { 2.54mm X 2.54mm }</b>
<b>Dimension { H, W, T } :</b>	<b>4.5" X 9.6" X 0.062"</b>
<b>Material :</b>	<b>CEM-1</b>
<b>Wire-Wrap Terminals :</b>	<b>T44, T46, T49 &amp; T68</b>
<b>Solder Connector :</b>	<b>R644</b>
<b>Wire-Wrap Socket Pins :</b>	<b>R32</b>
<b>Wire-Wrap Connector :</b>	<b>R644-3</b>
<b>Extender :</b>	<b>3690</b>
<b>Recommended Card Cage:</b>	<b><a href="#">CCK 13 Series Card Cage { Subracks }</a></b>
<b>UL Flammability Class :</b>	<b>94V - 0</b>