

[Return to Search](#)[Print Page](#)

Product Number: 13607

Order Abbreviation: 40S11N/BL 120V

General Description: Incandescent S11 Bulb Shape High Intensity Clear Finish Intermediate Base 40Watt 120V Blister Pack 12Bulbs Per Case 1Bulb Per Package

Product Information

Abbrev. With Packaging Info.	40S11NBL 120V 12/CS 1/SKU
Approx. Lumens	440
Average Rated Life (hr)	500
Base	Intermediate
Bulb	S11
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	1.375
Diameter (mm)	34.93
Filament	C-7A
Lamp Finish	Clear
Light Center Length - LCL (in)	1.625
Light Center Length - LCL (mm)	41
Maximum Overall Length - MOL (in)	2.313
Maximum Overall Length - MOL (mm)	58.7375
Nominal Voltage (V)	120.00
Nominal Wattage (W)	40.00

Additional Product Information