

# FM010

## TELCO Male Modular Connectors - RJ45 (Stranded)

Status: Available

### FUNCTIONAL NOTES:

This TELCO Modular Connector is for use with Flat Satin cable or Oval stranded cable. According to the manufacturer of this connector it will accept an Oval cable with an outer jacket size of 0.100 inches high by 0.350 inches wide plus or minus 0.010 inches. It will also accept a round cable with a Max 0.215 inch outside diameter. Wire gauges accepted are ,26,or 28 AWG.

.

### PRODUCT SPECIFICATIONS:

<b><i>Physical</i></b>	
<b>Dimensions</b>	0.850"L x 0.464"W x 0.314"H
<b>Connector Style</b>	RJ45
<b>Gender</b>	Male
<b>Termination Method</b>	Crimp Style
<b><i>Marketing</i></b>	
<b>Special Product Cross Reference</b>	EL08A (RJ45 Bulk Cable).
<b><i>Literature</i></b>	
<b>Manual Available?</b>	
<b>Manual Name</b>	
<b>Manual Date</b>	
<b>Schematic Vendor Name</b>	
<b>Schematic Available?</b>	
<b>Schematic Non-Disclosure Required?</b>	
<b>Schematic Date</b>	
<b>Additional Schematic Requirements</b>	
<b>Literature Comments</b>	
<b><i>Agency Compliance</i></b>	
<b>EIA/TIA</b>	