



Barrier Strip, 12 circuit, 30A, 300V



Features

- UL recognized for 30A, 300V
- CSA certified for 20A, 400V
- Torque Rating of 4.4 in-lbs
- Recessed screws and tubular contacts
- Connect stripped un-terminated solid or stranded wire
- Modular 12 circuits can be cut into smaller sections
- Plastic housing is UL flame rated to 94V-2
- Rated temperature to 105 degrees C

Models

Description	Catalog #
Barrier Strip, 12 circuit, 30A, 300V	89-610