



Sta-Kon®

Ring Terminal
T&B Catalog Number:

UPC Number:
Status:
Description:

RF717
 78621082094
 Active

Insulated Nylon Ring Terminal For Wire Range 4 Stud Size 1/4, Yellow
WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

Funneled Barrel Entry, Deep Internal Serrations, Brazed or overlapping seams.

General

Insulation Type	Insulated Nylon
Terminal Series	RF
Material	Copper
Finish	Electro -Tin Plated
Color	Yellow
Wire Range	4
Stud Size	1/4

Dimension Information

Maximum Insulation (inches)	.510
Stock Thickness	.04
A (inches)	1.76
B (inches)	.56
C (inches)	.36
M (inches)	1.49

Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-2

Tooling

Tool Charts	Available on Website
Application Tools	TBM6, TBM6S, ERG4007
Recommended Tool	TBM6S

Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	1000
Package Type	Bulk
T&B Sold in UOM	Each
T&B Weight Per UOM	2.3 lbs. per 100
Alternate Package Qty	RF4-14

Application Support

T&B Sales Drawings	wsd-000208
Overview	Available on Website

Wire Guide Tables

Available on Website

Notes

Not available on Mylar Tape.

Certifications



File Nbr:

E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com