

83900 Multi-Conductor - High-Temperature Thermocouple Wire



For more Information
please call

1-800-Belden1

**General Description:**

20 AWG solid conductors, FEP insulation, unshielded, FEP jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Conductors	AWG	Stranding	Conductor Material
1	20	Solid	Iron
1	20	Solid	Constantan

Total Number of Conductors: 2

Insulation**Insulation Material:**

Insulation Material	Wall Thickness (mm)
FEP - Fluorinated Ethylene Propylene	0.254

Outer Shield**Outer Shield Material:**

Outer Shield Material
Unshielded

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material
FEP - Fluorinated Ethylene Propylene

Overall Cable

Overall Nominal Diameter: 1.930 x 3.251 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -70°C To +200°C

Non-UL Temperature Rating: 200°C

Bulk Cable Weight: 19.347 Kg/Km

Min. Bend Radius/Minor Axis: 31.750 mm

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC(UL) Specification: PLTC, CL3P

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

83900 Multi-Conductor - High-Temperature Thermocouple Wire

CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
ANSI Specification:	MC 96.1-1982 Type J

Flame Test

UL Flame Test:	UL910 Steiner Tunnel
-----------------------	----------------------

Plenum/Non-Plenum

Plenum (Y/N):	Yes
----------------------	-----

Surface Printing (Overall)**Electrical Characteristics (Overall)****Nom. Conductor DC Resistance:**

Description	DCR @ 20°C (Ohm/km)
IRON	203.422
CONSTANTAN	1010.55

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
83900 001100	30 MT	0.907 KG	BROWN		2#20 TYPE J THERMOCOUPLE
83900 0011000	305 MT	6.350 KG	BROWN	C	2#20 TYPE J THERMOCOUPLE
83900 001500	152 MT	3.175 KG	BROWN		2#20 TYPE J THERMOCOUPLE

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 06-29-2011

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.