

SOLID PC 1919 13 T-2FSH



Sample photo

Order symbol: PC 1919 13 T-2FSH
Product nbr: 2539535
Description: Enclosure, PC
Remarks: Transparent hinged cover

EAN: 6418074052827
EI. number:
 Finland: 3435746
 Sweden: 2539535
 Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		188	188	130	Ingress Protection (EN 60529): IP 65
inch:		7.4	7.4	5.1	Impact Resistance (EN 62262): IK 08/09
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate		Halogen free (DIN/VDE 0472, Part 815): Yes	
Base colour:		RAL 7035		UV resistance: UL 508	
Cover colour:		Clear transparent		Flammability Rating (UL 746 C 5): UL 746C 5V	
Cover screws material:		Polyamide		Glow Wire Test (IEC 695-2-1) °C: 960	
Cover screws colour:		Grey		UL Type: UL TYPE 1, 3, 3S, 12	
Gasket material:		Polyurethane			
Temperatures:					Certificates:
Short term:		-40 ... 120 °C		Underwriters Laboratories	
Continuous:		-40 ... 80 °C		Fimko	
Short term:		-40 ... 250 °F		Europe EN 62208: 2003	
Continuous:		-40 ... 175 °F		UL Canada	
Accessories:					Gost R
EKHVT		Mounting plate			
EKHXT		Mounting plate Pertinax			
EKV 12		DIN-35 Mounting rail			

