

SOLID PC 2819 13 G



Sample photo

Order symbol: PC 2819 13 G
Product nbr: 5330360
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074005441
El. number:
Finland: 3423705
Italy: 7401020
Sweden: 2539410
Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		278	188	130	Ingress Protection (EN 60529): IP 66/67
inch:		10.9	7.4	5.1	Impact Resistance (EN 62262): IK 08/09
Materials:					
Material:		Polycarbonate			
Base colour:		RAL 7035			
Cover colour:		RAL 7035			
Cover screws material:		Polyamide			
Cover screws colour:		Grey			
Gasket material:		Polyurethane			
Temperatures:					
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
EKJVT		Mounting plate			
EKJXT		Mounting plate Pertinax			
EKV 12		DIN-35 Mounting rail			
EKV 22		DIN-35 Mounting rail			
EKJZR		Extension frame			
Certificates:					
		Underwriters Laboratories			
		Fimko			
		Europe EN 62208: 2003			
		UL Canada			
		Gost R			

