

SOLID PC 3819 13 G



Sample photo

Order symbol: PC 3819 13 G
Product nbr: 5330361
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074005489
El. number:
Finland: 3423709
Italy: 7401030
Sweden: 2539414
Norway: 2536321

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		378	188	130	Ingress Protection (EN 60529): IP 66/67
inch:		14.9	7.4	5.1	Impact Resistance (EN 62262): IK 08/09
Materials:					
Material:		Polycarbonate			
Base colour:		RAL 7035			
Cover colour:		RAL 7035			
Cover screws material:		Polyamide			
Cover screws colour:		Grey			
Gasket material:		Polyurethane			
Temperatures:					
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
EKMVT		Mounting plate			
EKMXT		Mounting plate Pertinax			
EKV 12		DIN-35 Mounting rail			
EKV 32		DIN-35 Mounting rail			
EKMZR		Extension frame			
		Certificates: Underwriters Laboratories Fimko Europe EN 62208: 2003 UL Canada Gost R			

