

SOLID PC 2828 13 G-2FSH



Sample photo

Order symbol: PC 2828 13 G-2FSH
Product nbr: 2539517
Description: Enclosure, PC
Remarks: Grey hinged cover

EAN: 6418074052728
El. number:
Finland: 3435728
Sweden: 2539517
Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		278	278	130	Ingress Protection (EN 60529): IP 65
inch:		10.9	10.9	5.1	Impact Resistance (EN 62262): IK 08/09
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Cover colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 746C 5V
Cover screws material:		Polyamide			Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:		Grey			UL Type: UL TYPE 1, 3, 3S, 12
Gasket material:		Polyurethane			Certificates:
Temperatures:					Underwriters Laboratories
Short term:		-40 ... 120 °C			Fimko
Continuous:		-40 ... 80 °C			Europe EN 62208: 2003
Short term:		-40 ... 250 °F			UL Canada
Continuous:		-40 ... 175 °F			Gost R
Accessories:					
EKOVT		Mounting plate			
EKOXT		Mounting plate Pertinax			
EKV 22		DIN-35 Mounting rail			
EKOZR		Extension frame			

SOLID 278x278x130-180

