




© FREESCALE SEMICONDUCTOR, INC.
ALL RIGHTS RESERVED.

MECHANICAL OUTLINE

PRINT VERSION NOT TO SCALE

TITLE: MAPLGA, THIN PROFILE,
FINE PITCH, 44 I/O, 5 X 5 PKG,
0.65 MM PITCH (LAMINATE QFN)


DOCUMENT NO: 98ASA00239D

REV: C

CASE NUMBER: 2141-01

05 APR 2011

STANDARD: NON-JEDEC



DETAIL D
VIEW ROTATED 90° CW

© FREESCALE SEMICONDUCTOR, INC. ALL RIGHTS RESERVED.	MECHANICAL OUTLINE		PRINT VERSION NOT TO SCALE	
TITLE: MAPLGA, THIN PROFILE, FINE PITCH, 44 I/O, 5 X 5 PKG, 0.65 MM PITCH (LAMINATE QFN)	DOCUMENT NO: 98ASA00239D		REV: C	
	CASE NUMBER: 2141-01		05 APR 2011	
	STANDARD: NON-JEDEC			

NOTES:

1. ALL DIMENSIONS IN MILLIMETERS.

2. DIMENSIONING AND TOLERANCING PER ASME Y14.5M–1994.

 3. DIMENSION APPLIES TO ALL LEADS AND FLAG AREAS.

 4. PARALLELISM MEASUREMENT SHALL EXCLUDE ANY EFFECT OF MARK ON TOP SURFACE OF PACKAGE.

© FREESCALE SEMICONDUCTOR, INC. ALL RIGHTS RESERVED.	MECHANICAL OUTLINE	PRINT VERSION NOT TO SCALE	
TITLE: MAPLGA, THIN PROFILE, FINE PITCH, 44 I/O, 5 X 5 PKG, 0.65 MM PITCH (LAMINATE QFN)	DOCUMENT NO: 98ASA00239D		REV: C
	CASE NUMBER: 2141–01		05 APR 2011
	STANDARD: NON–JEDEC		