

Black Box Products

Cables > Computer & Data Cables



Extended-Distance/Quiet Cable with Die-Cast Removable Metallic EMI/RFI Hoods, Stranded, DB25, NEC® CL2, 25 (12 1/2 Pairs)—Pins 1–25, 5-ft. (1.5-m), MM



Maximum protection for short RS-232 runs in noisy environments.

EBN25C-0005-MM

Extended Double Diamond™ Warranty Available (Lifetime)

Product Highlights

- Made for short runs in extra-noisy environments.
- 100% foil shield plus a tinned copper-braid.
- 24 AWG stranded copper conductors.
- Guaranteed for life!

Details

Description

Extended-Distance/Quiet Cable with Die-Cast Removable Metallic EMI/RFI Hoods, Stranded, DB25, NEC® CL2, 25 (12 1/2 Pairs)—Pins 1–25, 5-ft. (1.5-m), MM

Quick Facts

- Made for short runs in extra-noisy environments.
- 100% foil shield plus a tinned copper-braid.
- 24 AWG stranded copper conductors.
- Guaranteed for life!

Further Details

- Protect your data from end to end with a 100% foil shield plus an 85% tinned copper-braided shield.
- Ideal for industrial environments. EMI/RFI-resistant hoods stop damaging noise where cables are most vulnerable—at the connection.
- In extra-quiet environments, use these cables for long runs—up to 500 feet (152.4 m) at 9600 bps.
- Removable hoods enable convenient testing or repinning.
- In extra-quiet environments, use it for long runs up to 500 feet (152.4 m) at 9600 bps.
- Also available with nonremovable hoods.

Noise bursts can come from just about anywhere—fluorescent lighting, radio or cellular transmitters, electrical wiring, and other data cables. Electrical energy from any one of them can scramble your data.

If you have long cable runs or you work in a noisy area, you need the cable that ensures every bit of your document will be accounted for when it arrives at the printer, the modem, or your PC. Our high-quality ED/Q Cable with Die-Cast Removable Metallic EMI/RFI Hoods gives you extra protection at the ends of the cable. Remove the hoods for convenient testing or repinning.

Tech Spec

Technical Specifications for Extended-Distance/Quiet Cable with Die-Cast Removable Metallic EMI/RFI Hoods, Stranded, DB25, NEC® CL2, 25 (12 1/2 Pairs)—Pins 1–25, 5-ft. (1.5-m), MM:

Cable Construction	— PVC
Conductor Gauge	— 24 AWG (7 x 32) stranded copper
Mutual Capacitance	— 12 pF/ft.
Resistance	— 30 ohms/1000 ft.
Shield	— 100% aluminum foil, 85% tinned copper braid
RoHS	— Yes