

## Black Box Products

---

### Cables > Computer & Data Cables



### RS-232 ED/Q Cable with Molded Hoods, 35-ft. (10.6-m)



Transmit RS-232 data up to 500 feet at 9600 bps!

EMN25C-0035-MF

---

Extended Double Diamond™ Warranty Available  
(Lifetime)

#### Product Highlights

- Feature a foil shield plus an 85% tinned copper braid for extra protection against EMI/RFI transmissions in noisy office environments.
- Molded, nonremovable hoods.
- Guaranteed for life!

## Details

### Description

RS-232 Extended-Distance/Quiet Cables with Molded Hoods, 25 Conductors (12 1/2 Pairs), M/F

### Quick Facts

- Feature a foil shield plus an 85% tinned copper braid for extra protection against EMI/RFI transmissions in noisy office environments.
- Molded, nonremovable hoods.
- Guaranteed for life!

### Further Details

- NEC® CL2 compliant. For connecting computers inside a building. Not for use in risers or plenums.
- Low capacitance.
- All conductors are straight wired for connecting the serial output of your computer to a switch box.
- Male screw locks are standard.
- Perfect for industrial applications near heavy machinery or in environments with high EMI/RFI.

## Tech Spec

### Technical Specifications for RS-232 ED/Q Cable with Molded Hoods, 35-ft. (10.6-m):

<b>Cable Construction</b>	— PVC
<b>Capacitance</b>	— 12 pF/ft. ± 2 pF/ft.
<b>Conductor Gauge</b>	— 24 AWG (7 x 32), stranded
<b>Outside Diameters</b>	— 0.245", 0.260", 0.335", 0.365", 0.430"
<b>Resistance</b>	— 30 ohms/1000 ft.