



ESD TORX SCREWDRIVERS AND SOCKET WRENCHES

with slim, ergonomically formed handles from black, **conductive** plastic. The swivel top guarantees a precise working without exhaustion.

Blade: chrome vanadium, hardened over its full length, chrome-plated, black tip, "L" with bore-hole in the tip

Handle: impact-resistant, **conductive** black plastic, electrostatic discharge according to DIN EN 100015/1

TORX-screwdrivers



No.	Size	Blade length mm	for metric thread	Handle length mm	Weight
6-656	T 1	50	M 0.9	90	12 g
6-657	T 2	50	M 1.0-1.2	90	12 g
6-658	T 3	50	M 1.2-1.4	90	12 g
6-659	T 4	50	M 1.4-1.6	90	12 g
6-661	T 5	50	M 1.6-2	90	12 g
6-662	T 6	50	M 2	90	16 g
6-663 L	T 7	50	M 2.5	90	16 g
6-664 L	T 8	60	M 2.5	90	16 g
6-665 L	T 9	60	M 3	90	19 g
6-666 L	T 10	60	M 3-3.5	90	21 g

extra long TORX screwdrivers with conductive special-square pattern handle

6-675 L	T 10	300	M 3-3.5	92 x 21	60 g
6-676 L	T 15	300	M 3.5-4	92 x 21	65 g
6-677 L	T 20	300	M 4-5	100 x 21	75 g



6-660



6-660 6-piece TORX-screwdriver set,

in a practical table support from **conductive** material

Contents: 6 TORX-screwdrivers No. 6-661, 6-662, 6-663, 6-664, 6-665, 6-666

Weight: 163 g

Socket wrenches



No.	A/F mm	Blade length mm	Handle length mm	Weight
6-611	1.5	70	90	15 g
6-612	2.0	70	90	15 g
6-613	2.5	70	90	18 g
6-614	3.0	70	90	18 g
6-615	3.2	70	90	18 g
6-616	3.5	70	90	18 g
6-617	4.0	70	90	18 g
6-618	4.5	70	90	19 g
6-619	5.0	70	90	19 g
6-621	5.5	70	90	20 g



6-610

6-610 6-piece socket wrench set

in a practical table support from **conductive** material

Contents: 6 Socket wrenches No. 6-612, 6-614, 6-617, 6-618, 6-619, 6-621

Weight: 180 g