

Model A95U User Guide

MODEL A95U LINE MATCHING TRANSFORMER

This reversible transformer matches low- or high-impedance microphones to high- or low-impedance inputs. The transformer permits use of very long microphone cables with either low- or high-impedance microphones. However, when connecting a high-impedance microphone, limit the cable length between the microphone and the transformer to 4.6 m (15 ft). The cable from the transformer to the low-impedance input can be any desired length.

The transformer prevents high-frequency loss, level loss, and pickup of noise and hum. The A95U comes furnished with a three-pin XLR connector on the low-impedance end, with a 1/4 in. phone plug and phone jack adapter on the high-impedance end.

Case

Full magnetic shield, steel with gray enamel finish

Dimensions

19 mm (3/4 in.) diameter; 89 mm (31/2 in.) long without adapters


LOW-IMPEDANCE SELECTION

The A95U comes factory preset with the low-impedance end intended for use with microphones or inputs rated 75 to 300 ohms. For microphones or input rated at 19 to 75 ohms, make the following changes.

 Remove the low-impedance XLR plug by turning the lock screw counterclockwise and withdrawing the XLR plug from the case.



- Unsolder the YELLOW lead from pin 3 and insulate the bare wire at the end of the lead with the insulator from the ORANGE lead.
- 3. Solder the ORANGE lead to pin 3.
- Rotate the XLR plug three turns to twist the leads, then replace the XLR plug in the case. Tighten the lock screw to secure the XLR plug in place (turning clockwise).



LOW IMPEDANCE

HIGH IMPEDANCE

SPECIFICATIONS

Frequency Response

Flat, 20 Hz to 20 kHz. Response at 20 Hz no more than 3 dB down from flat.

Impedance

Low impedance: 75 to 300 Ω (supplied) or 19 to 75 Ω

Medium impedance: High (41 k Ω with 150- Ω source on 75-to-300 Ω winding.)

DC Resistance

Low impedance:75 to 300 Ω – 75 Ω 19 to 75 Ω – 37.5 Ω

High impedance: 4300 Ω

Voltage Ratio	19 to 75 Ω	75 to 300 Ω
Low impedance to high impedance:	+28 dB	+22 dB
High impedance to low impedance:	-28 dB	-22 dB

Maximum Recommended Input Levels

Source Impedance	Winding Being Driven	Maximum Level
33 Ω	19 to 75 Ω	0.5 V
200 Ω	75 to 300 Ω	1.0 V
$600~\Omega$	High impedance	10 V
5,000 Ω	High impedance	10 V
33,000 Ω	High impedance	10 V

LIMITED WARRANTY

Shure Incorporated ("Shure") hereby warrants to the original consumer purchaser only that this product will be free in normal use of any defects in materials and workmanship for a period of two (2) years from the consumer's original date of purchase directly from Shure or from a Shure-authorized reseller. At its sole option, Shure will repair or replace the defective product and promptly return it to you. In order for this warranty to be valid, the consumer must, at the time the product is returned, provide proof of purchase in the form of the original purchase receipt directly from Shure or from a Shure-authorized reseller. If Shure elects to replace the defective product, then Shure reserves the right to replace the defective product with another product of the same model or a model of at least comparable quality and features in Shure's sole determination.

If you believe this product is defective within the warranty period, carefully repack the unit, insure it and return it with proof of purchase, postage prepaid, to Shure Incorporated, Attention: Service Department, at the address below.

Outside of the United States, return the product to your dealer or Authorized Service Center. Addresses are listed on **www.Shure.com** or can be obtained by contacting Shure at the address listed below.

This warranty is not transferable. This warranty does not apply in cases of abuse or misuse of the product, use contrary to Shure's instruction, ordinary wear and tear, an act of God, negligent use, purchase from a party other than Shure or a Shure-authorized reseller, unauthorized repair, or modification of the product.

ALL IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE ARE HEREBY DISCLAIMED TO THE EXTENT PERMITTED UNDER APPLICABLE LAWS AND, TO THE EXTENT NOT PERMITTED, ARE HEREBY LIMITED TO THE DURATION AND TERMS OF THIS WARRANTY

SHURE ALSO HEREBY DISCLAIMS ALL LIABILITY FOR INCIDENTAL, SPECIAL, OR CONSEQUENTIAL DAMAGES.

Some states do not allow limitations on how long an implied warranty lasts, or the exclusion or limitation of incidental or consequential damages, so the above limitation may not apply to you. This warranty gives you specific legal rights, and you may have other rights which vary from state to state.

This warranty does not restrict the rights of the consumer mandated under applicable laws.

THIS WARRANTY SUPERSEDES ALL OTHER WARRANTIES THAT ARE ASSOCIATED OR INCLUDED WITH THIS PRODUCT.

Shure Incorporated Attention: Service Department 5800 W. Touhy Avenue Niles. IL 60714-4608 U.S.A.



SHURE Incorporated http://www.shure.com
United States, Canada, Latin America, Caribbean:
5800 W. Touhy Avenue, Niles, IL 60714-4608, U.S.A.
Phone: 847-600-2000 U.S. Fax: 847-600-1212 Intl Fax: 847-600-6446
Europe, Middle East, Africa:
Shure Europe GmbH, Phone: 49-7131-72140 Fax: 49-7131-721414
Shure Asia Limited, Phone: 852-2893-4290 Fax: 852-2893-4055