




REV.		REVISIONS		DATE
A		New Release		10/11/05

Insulator: PBT+30% Glass Fiber,
UL94V-0 Rate
Shell: Cold Rolled Steel, Tin Plated



Dimension of Crimp Type Connector



Specification:

1. Plastic Housing: ABS, Gray
2. Jackscrew: Nickel Plated, #4-40 UNC TYP. 2
3. Contact: Phosphor Bronze, Gold Plated
4. Wire Lead: AWG26, Crimping Male/Female Terminal
5. DB09 Connector: Male/Female, Crimp Type

DRAWN	S. C. YANG	10/11/05
APPROVED		
TITLE		
DB-9 to Modular Adapter		
PART NO.	0110-8/0210-8	REV. A
SCALE:	1:1	SHEET 1 OF 1
DRAWING NO.	E051296-U	